


Siemens
EcoTech



Labeling plate for snapping on or gluing to label holder, label size 12.5x27mm, silver label, black font, with inscription: Fast



product brand name	SIRIUS ACT		
product designation	Labeling plate		
product type designation	3SU1		
General technical data			
protection class IP	IP66, IP67, IP69(IP69K)		
shock resistance for railway applications according to EN 61373	Category 1, Class B		
vibration resistance for railway applications according to EN 61373	Category 1, Class B		
Substance Prohibittance (Date)	10/01/2014		
Net Weight	1 g		
Ambient conditions			
ambient temperature			
• during operation	70 ... -25 °C		
• during storage and transport	80 ... -40 °C		
Environmental footprint			
Environmental Product Declaration(EPD)	Yes		
global warming potential [CO2 eq] total	0.787 kg		
global warming potential [CO2 eq] during manufacturing	0.566 kg		
global warming potential [CO2 eq] during operation	0.235 kg		
global warming potential [CO2 eq] after end of life	-0.015 kg		
Installation/ mounting/ dimensions			
height	12.5 mm		
width	27 mm		
Accessories			
material of accessory	Plastic		
fastening method of label	snap on / stick		
marking of the name plate for command devices	Fast		
shape of the name plate for command devices	rectangular		
color of the label	silver(plate); black (text)		
Approvals Certificates			
General Product Approval		Test Certificates	Maritime application



[Type Test Certificates/Test Report](#)



Maritime application



[Confirmation](#)



Environment



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0AC81-0EE0>

Cax online generator



<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0AC81-0EE0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0AC81-0EE0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0AC81-0EE0&lang=en



last modified:

4/2/2025 