



Pivoting lever drive (Please order lever separately) for position switch 3SE51/3SF11, for 40/56/56XL mm, Switch points according to EN 50041. The switching direction the lever is on left / right or left only or only to the right. Delivery state ist right / left.

product brand name		SIRIUS	
product designation		Part-turn actuator for position switch 3SE51/3SF11	
product type designation		3SE5	
manufacturer's article number			
• of the supplied actuator head for position switches		3SE5000-0AH00	
General technical data			
shock resistance			
• according to IEC 60068-2-27		30g / 11 ms	
vibration resistance			
• according to IEC 60068-2-6		0.35 mm/5g	
material of the enclosure of the switch head		plastic	
reference code according to IEC 81346-2		T	
active principle		mechanical	
Substance Prohibitance (Date)		07/01/2006	
Net Weight		0.032 kg	
minimum actuating torque in directions of actuation		0.25 N·m	
Ambient conditions			
ambient temperature			
• during operation		-25 ... +85 °C	
• during storage		-40 ... +90 °C	
explosion protection category for dust		none	
Enclosure			
coating of the enclosure		Other types	
Drive Head			
design of the actuating element		Twist actuator, without lever or rod	
standard-compliant actuator head		EN 50041	
Installation/ mounting/ dimensions			
mounting position		any	
fastening method		lockable plug-in fixing	
design of the interface for safety-related communication		without	
Communication/ Protocol			
design of the interface		without	
Approvals Certificates			
General Product Approval		Test Certificates	other



[Type Test Certificates/Test Report](#)



other	Environment
-------	-------------

[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5000-0AH00>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5000-0AH00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SE5000-0AH00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5000-0AH00&lang=en



last modified:

4/2/2025