

box terminal; 3 units accessory for: 3VA13/14; 3VA23/24



Model	
product brand name	SENTRON
product designation	box terminal 3 units
accessories	Box terminal
General technical data	
designation / of the terminal	TS1.5
type of electrical connection / with control wire tap	No
Mechanical Design	
Net Weight	431 g
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	35 mm ²
• for copper cable / stranded / maximum	300 mm ²
type of connectable conductor cross-sections / of the laminated conductor rails	
• minimum	2 x 20mm x 1mm, 2 x 24mm x 1mm
• maximum	10 x 20mm x 1mm, 10 x 24mm x 1mm
stripped length	26.5 mm
tightening torque / when using copper cables	
• stranded	35 - 95 mm ² : 16 Nm; 120 - 300 mm ² : 28 Nm
• finely stranded	35 - 95 mm ² : 16 Nm, 120 - 240 mm ² : 28 Nm
• finely stranded / with core end processing	35 - 95 mm ² : 16 Nm, 120 - 240 mm ² : 28 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	1.05 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	1/0 AWG
• for copper cable / stranded / maximum	500 kcmil
tightening torque / when using copper cables	
• stranded	1/0 - 4/0: 140 lb-in; 250 - 500 kcmil: 248 lb-in
Certificates	
General Product Approval	EMV



[Confirmation](#)

[Miscellaneous](#)



Test Certificates	Maritime application	other	Environment
Type Test Certificates/Test Report		Confirmation	Miscellaneous
			 Environmental Confirmations

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9483-0JA13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9483-0JA13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9483-0JA13

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>



last modified:

8/8/2025 

