



Control Power Transformer, 50va, PRI 380v, SEC 24v, Kit

product brand name	Control Power Transformer
design of the product	Control power voltage
special product feature	Complete kit
General technical data	
weight [lb]	3.5 lb
Height x Width x Depth [in]	4 × 3 × 3.64 in
ambient temperature [°F] during operation	-4 ... +104 °F
ambient temperature during operation	-20 ... +40 °C
country of origin	Mexico
operating apparent power rated value	50 VA
Enclosure	
design of the housing	Open
Mounting/wiring	
mounting position	Any
fastening method	Surface mounting
type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)
type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
Inputs/ Outputs	
input variables of primary voltage	240/480vac
output dimensions of secondary voltage	120vac
phase number of the inputs	1
electrical input frequency	50 ... 60 Hz
input voltage _1	240 V
input voltage _2	480 V
phase number of the outputs	1
electrical output frequency	60 ... 50 Hz
output voltage _1 rated value	120 V
certificate of suitability	UL / CSA
Approvals Certificates	
General Product Approval	



[China RoHS](#)

[Manufacturer Declaration](#)

[Confirmation](#)



EG-Konf.



General Product Approval

[Miscellaneous](#)

[Declaration of Con-
formity](#)



General Product Approval

EMV



[Miscellaneous](#)

[Metrological Approval](#)

[TUEV](#)



EMV

For use in hazardous locations

Functional Safety



[FM](#)

[CCC-Ex](#)



[Type Examination Cer-
tificate](#)

[TUEV](#)

Radio Equipment
Type Approval Certi-
ficate

Test Certificates

Maritime application

other

Food, Pharmaceut-
ical, Medical

Dangerous goods

[Miscellaneous](#)



[CCS \(China Classifica-
tion Society\)](#)

[Confirmation](#)

[Drinking Water Ap-
proval](#)

[Dangerous goods in-
formation](#)

Environment

Siemens
EcoTech



[Environmental Con-
firmations](#)

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:KT8050P>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:KT8050P>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:KT8050P&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:KT8050P/certificate>

last modified:

10/23/2025