



Figure similar

!!! Phased-out product !!! The preferred successor is 3RQ2000-1AW00. Coupling relays in industrial enclosure 1 change-over contact Combination voltage 24 V and 110-120 V AC/DC Screw terminal

product brand name	SIRIUS
product designation	Coupling relay in industrial enclosure
product type designation	3RS18
General technical data	
switching behavior	monostable
reference code according to IEC 81346-2	K
Substance Prohibitance (day/month/year)	11/01/2009
SVHC substance name	Lead CAS-No. 7439-92-1
Net Weight	0.12 kg
control supply voltage 1 at AC	
• at 50 Hz rated value	24 V
• at 50 Hz	110 ... 120 V
• at 60 Hz rated value	24 V
• at 60 Hz	110 ... 120 V
control supply voltage 1 at DC rated value	24 V
Switching Function	
design of the switching function	changeover switch
Mechanical data	
product component plug-in socket	No
design of the relay operating mechanism	poled
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	1
Main circuit	
type of voltage	AC/DC
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
Connections/ Terminals	
type of electrical connection	screw terminal
Installation/ mounting/ dimensions	
fastening method	screw and snap-on mounting onto 35 mm DIN rail
height	83 mm
width	22.5 mm
depth	91 mm
Ambient conditions	

ambient temperature during operation	-25 ... +60 °C
--------------------------------------	----------------

Approvals Certificates

Environment	General Product Approval
-------------	--------------------------

[Environmental Confirmations](#)



EMV	Test Certificates	other
-----	-------------------	-------



[Type Test Certificates/Test Report](#)

[Miscellaneous](#)

[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RS1800-1AQ00>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RS1800-1AQ00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RS1800-1AQ00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RS1800-1AQ00&lang=en



