

**TELEMECANIQUE CONTACTOR SUPPRESSOR**

Varistor, 250VAC/DC

Art.No.: 26187

Weight: 0.003 kg



Country of origin: CZ

Model designation: PZV 250

230 V AC/DC

VDR

For other configurations and voltages, please inquire.

**Link to Product****Illustration**

Product may differ from Image

**Header**

Material short text

PZV 250

**Commercial data**

URL Webshop

<https://shop.murrelektronik.com/26187>

|                                                 |                           |
|-------------------------------------------------|---------------------------|
| GTIN                                            | 4048879018104             |
| ECLASS-6.0                                      | 27371013                  |
| ECLASS-6.1                                      | 27371013                  |
| ECLASS-7.0                                      | 27371013                  |
| ECLASS-7.1                                      | 27371013                  |
| ECLASS-8.0                                      | 27371013                  |
| ECLASS-8.1                                      | 27371013                  |
| ECLASS-9.0                                      | 27371013                  |
| ECLASS-9.1                                      | 27371013                  |
| ECLASS-10.0.1                                   | 27371013                  |
| ECLASS-10.1                                     | 27371013                  |
| ECLASS-11.0                                     | 27371013                  |
| ECLASS-11.1                                     | 27371013                  |
| ECLASS-12.0                                     | 27371013                  |
| ECLASS-13.0                                     | 27371013                  |
| ECLASS-14.0                                     | 27371013                  |
| ETIM-5.0                                        | EC002498                  |
| ETIM-6.0                                        | EC002498                  |
| ETIM-7.0                                        | EC002498                  |
| ETIM-8.0                                        | EC002498                  |
| customs tariff number                           | 85363010                  |
| EAN                                             | 4048879018104             |
| Packaging unit                                  | 1                         |
| <b>Electrical data</b>                          |                           |
| Damping factor                                  | 1.5× UN                   |
| <b>Electrical data   Input</b>                  |                           |
| Input voltage AC                                | 250 V                     |
| <b>Installation   Connection</b>                |                           |
| Connection information                          | flexible connection wires |
| <b>Device protection   Media</b>                |                           |
| Flame resistance                                | flame retardant           |
| <b>Mechanical data   Material data</b>          |                           |
| Material housing                                | Plastic                   |
| Combustibility class housing (UL94)             | V-0                       |
| <b>Mechanical data   Mounting data</b>          |                           |
| Height                                          | 13 mm                     |
| Width                                           | 23 mm                     |
| Depth                                           | 7,5 mm                    |
| <b>Environmental characteristics   Climatic</b> |                           |
| Operating temperature min.                      | -20 °C                    |
| Operating temperature max.                      | 70 °C                     |