

MODLINK MSDD DATA INSERT

2xSUB-D9 female/female

Art.No.: 4000-68000-0260000  
Weight: 0.040 kg  
Country of origin: DE  
Model designation: Fr. Modul MSDD 2x9 pol. Bu/Bu

SUB-D9; SUB-D9  
2× SUB-D9 (female/female)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFr. Modul MSDD 2x9 pol. Bu/Bu

Commercial data

|               |                                                    |
|---------------|----------------------------------------------------|
| URL Webshop   | https://shop.murrelektronik.com/4000-68000-0260000 |
| GTIN          | 4048879038041                                      |
| ECLASS-6.0    | 27189217                                           |
| ECLASS-6.1    | 27189217                                           |
| ECLASS-7.0    | 27189217                                           |
| ECLASS-7.1    | 27189217                                           |
| ECLASS-8.0    | 27189217                                           |
| ECLASS-8.1    | 27189217                                           |
| ECLASS-9.0    | 27182806                                           |
| ECLASS-9.1    | 27189217                                           |
| ECLASS-10.0.1 | 27182806                                           |
| ECLASS-10.1   | 27182806                                           |
| ECLASS-11.0   | 27182806                                           |
| ECLASS-11.1   | 27182806                                           |
| ECLASS-12.0   | 27182806                                           |
| ECLASS-13.0   | 27182806                                           |
| ECLASS-14.0   | 27182806                                           |

|                       |               |
|-----------------------|---------------|
| ETIM-5.0              | EC002625      |
| ETIM-6.0              | EC002625      |
| ETIM-7.0              | EC002625      |
| ETIM-8.0              | EC002625      |
| customs tariff number | 85366990      |
| EAN                   | 4048879038041 |
| Packaging unit        | 1             |
| customs tariff number | 85366990      |
| EAN                   | 4048879038041 |
| Packaging unit        | 1             |

#### Mechanical data | Mounting data

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 15 mm |

#### Environmental characteristics | Climatic

|                                          |        |
|------------------------------------------|--------|
| Ambient temperature (storage, transport) | -30 °C |
|------------------------------------------|--------|

#### SUB-D9

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Family construction form              | SUB-D9                                         |
| Gender                                | Female                                         |
| No. of poles                          | 9                                              |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| Family type Back side                 | SUB-D9                                         |
| Gender Rear                           | Female                                         |
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating current                     | 3 A                                            |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Current operating max. (UL)           | 175 mA                                         |