

**Modlink MSDD-set: Frame 4000-68123-0000000,**

insert 4000-68000-0090000 + 4000-68000-1210000

Art.No.: 4000-68123-0091210

Weight: 0.645 kg

Country of origin: CZ

Model designation: MSDD\_2MV\_AUSTRALIEN\_RJ45+BL\_

[Link to Product](#)**Illustration**



Product may differ from Image

#### Header

Material short text MSDD\_2MV\_AUSTRALIEN\_RJ45+BL\_

#### Commercial data

|                       |                                                                                                                     |
|-----------------------|---------------------------------------------------------------------------------------------------------------------|
| URL Webshop           | <a href="https://shop.murrelektronik.com/4000-68123-0091210">https://shop.murrelektronik.com/4000-68123-0091210</a> |
| GTIN                  | 4048879378062                                                                                                       |
| ECLASS-6.0            | 27189217                                                                                                            |
| ECLASS-6.1            | 27189217                                                                                                            |
| ECLASS-7.0            | 27189217                                                                                                            |
| ECLASS-7.1            | 27189217                                                                                                            |
| ECLASS-8.0            | 27189217                                                                                                            |
| ECLASS-8.1            | 27189217                                                                                                            |
| ECLASS-9.0            | 27182806                                                                                                            |
| ECLASS-9.1            | 27189217                                                                                                            |
| ECLASS-10.0.1         | 27182806                                                                                                            |
| ECLASS-10.1           | 27182806                                                                                                            |
| ECLASS-11.0           | 27182806                                                                                                            |
| ECLASS-11.1           | 27182806                                                                                                            |
| ECLASS-12.0           | 27182806                                                                                                            |
| ECLASS-13.0           | 27182806                                                                                                            |
| ECLASS-14.0           | 27182806                                                                                                            |
| ETIM-5.0              | EC002625                                                                                                            |
| ETIM-6.0              | EC002625                                                                                                            |
| ETIM-7.0              | EC002625                                                                                                            |
| ETIM-8.0              | EC002625                                                                                                            |
| customs tariff number | 85389099                                                                                                            |
| EAN                   | 4048879378062                                                                                                       |
| Packaging unit        | 1                                                                                                                   |
| customs tariff number | 85389099                                                                                                            |
| EAN                   | 4048879378062                                                                                                       |
| Packaging unit        | 1                                                                                                                   |

#### Frame

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Material housing                              | Fine zinc die casting |
| Coating housing                               | surface finished      |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |

|                            |        |
|----------------------------|--------|
| Operating temperature max. | 60 °C  |
| Storage temperature min.   | -25 °C |

#### Australia

|                               |                    |
|-------------------------------|--------------------|
| Connection                    | Screw terminals SK |
| No. of poles                  | PE                 |
| Connections per pole          | 2                  |
| Protection contact present    | Yes                |
| Connection cross section max. | 4 mm <sup>2</sup>  |
| AWG number max.               | 12                 |
| Operating voltage AC          | 240 V              |
| Operating current             | 15 A               |

#### RJ45

|                                       |                   |
|---------------------------------------|-------------------|
| Family construction form              | RJ45              |
| Looking techniques                    | Snap-in connector |
| Cable category min.                   | Cat5e             |
| Family type Back side                 | RJ45              |
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |