



TREE 6TX METALL - UNMANAGED SWITCH - 6 PORTS

Art.No.: 58172
Weight: 0.383 kg
Country of origin: TW
Model designation: Tree 6TX Metal

6 port unmanaged switch
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Tree 6TX Metal
Commercial data	
URL Webshop	https://shop.murrelektronik.com/58172
GTIN	4048879339728
ECLASS-6.0	19170106
ECLASS-6.1	19170106

ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
ETIM-5.0	EC000734
ETIM-6.0	EC000734
ETIM-7.0	EC000734
ETIM-8.0	EC000734
customs tariff number	85176200
EAN	4048879339728
Packaging unit	1

Electrical data | Supply

Operating voltage DC min.	9 V
Operating voltage DC max.	30 V

Industrial Communication

Data transmission rate max.	100 Mbit/s
-----------------------------	------------

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	Yes
Switch type	unmanaged
duplex	Full duplex
Auto-negotiation	Yes
Auto-crossover	Yes

Diagnostics

Alarm contact	No
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP40
Invers-polarity protection	Yes
Over voltage protection	Yes

Mechanical data | Material data

Material housing	Metal
Color housing	black

Mechanical data | Mounting data

Height	90,6 mm
Width	45,2 mm
Depth	78,7 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Connection type 3

Connection type 1	6
Connection type 2	X1

Connection type 3	X1
Family construction form	RJ45
No. of poles	8
Gender	female
Color contact carrier	black
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Family construction form	terminal
No. of poles	3
Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	0 V
PIN 3	24 V DC (UB 1)
Family construction form	terminal
No. of poles	3
Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	0 V
PIN 3	24 V DC (UB 2)