MVP-METALL, 4XM12, 5POLE, M23 19POL. CON.

Connector exit frontside


Art.No.: 8000-54522-0000000
Weight: 0.320 kg
Country of origin: CZ
Model designation: MVP12M-KK4F-XA


4-way, 5-pole
M23 plug connection, 19-pole
Without LED for analog signals up to 48 V AC/DC
Replaces identical product (Art.No. 27531)


Link to Product

Illustration











The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-08-15





Product may differ from Image

Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-54522-0000000
GTIN	4048879352864
EU-Customs tariff number	85366990
US-Customs tariff number	8536694020
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440108
ECLASS-9.1	27440108
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
ETIM-9.0	EC002585
ETIM-10.0	EC002585
customs tariff number	85366990
EAN	4048879352864
Packaging unit	1

Electrical data | Supply	
Operating voltage AC max.	48 V
Operating voltage DC max.	48 V
Current operating per contact max.	4 A
Total current max.	7,5 A

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-08-15

Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67, IP68, IP65
Mechanical data | Material data	
housing	Zinc die-casting
Coating housing	Nickeled
Environmental characteristics | Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	80 °C
Connection type 2	
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	+
PIN 2	NC S 2
PIN 3	-
PIN 4	NO S 1
PIN 5	PE
Family construction form	M23
No. of poles	19
Coding	A
Gender	male
Color contact carrier	black
PIN 3	GY
PIN 4	RD / BU
PIN 5	GN
PIN 6	BU
PIN 7	GY / PK
PIN 8	WH / GN
PIN 12	YE / GN
PIN 14	BN / GN
PIN 15	WH
PIN 16	YE
PIN 19	BN

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-08-15