


# Detailed Specifications & Technical Data



## METRIC MEASUREMENT VERSION

### AX102411 Faceplates and Panels - MediaFlex Keyconnect Style Insert 2-port, Flush



For more Information  
please call

1-800-Belden1



#### General Description:

Kit of 10 MediaFlex KeyConnect Module Insert, 2-port, flush, elec.white

#### Usage (Overall)

##### Suitable Applications:

- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200

##### Related Parts:

- Compatible with 10GX, CAT6+ and CAT5E Keyconnect-style Modular Jacks and Keyconnect Multimedia Modules

#### Physical Characteristics (Connectivity)

##### Capacity

Max. Capacity: 2 Inserts

##### Access

Front Connection: Flush

##### Dimensions

###### Dimensions:

| Height (mm) | Width (mm) | Depth (mm) |
|-------------|------------|------------|
| 23.495      | 52.070     | 14.986     |

##### Materials

###### Materials:

| Description | Material          |
|-------------|-------------------|
| Inserts     | Plastic - UL94V-0 |

##### Color

Color: Elec. White

##### Weight

Weight: 0.054 kg

##### Packaging

Packaging: 10 inserts packaged in a suitable plastic bag

#### Mechanical Characteristics (Connectivity)

Connector/Hardware Retention: 88.964 N

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Tool Compatibility: Termination Station (AX101852), Release Tool (AX101185)

#### Applicable Specifications and Agency Compliance (Overall)

##### Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MII Order #39 (China RoHS): Yes

Safety Listing: ACA, Bi-national Standard Listed

##### Suitability

Suitability - Indoor: Yes

#### Transmission Characteristics (Connectivity)

#### Notes (Overall)

Notes: For proper installation refer to Installation Guide PX102063 available on our web site at <http://www.belden.com>

# Detailed Specifications & Technical Data



## METRIC MEASUREMENT VERSION

### AX102411 Faceplates and Panels - MediaFlex Keyconnect Style Insert 2-port, Flush

#### Product Family

##### Part Numbers:

| Item Number | Color       |
|-------------|-------------|
| AX102410    | Almond      |
| AX102411    | Elec. White |
| AX104482    | Grey        |
| AX102737    | Black       |

#### Put Ups and Colors:

| Item #   | Putup | Ship Weight | Color | Notes | Item Desc                      |
|----------|-------|-------------|-------|-------|--------------------------------|
| AX102411 | 1 EA  | 0.120 LB    |       |       | KIT MFLEX KCONN INSERTS(10/PK) |

Revision Number: 0 Revision Date: 08-08-2012

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.