

Product: [Adapter Cable, RJ11/RJ45](#)



This adapter cable in conjunction with a Belden terminal cable with RJ45 connector allows a local connection from an external management station to the serial interface of a network device.

Product Description

Adapter Cable to convert from RJ45 8 pin to RJ11 6 pin. It can be applied with RJ45 to USB Terminal Cable: RJ11 – RJ45 (942 261-001) via 1:1 coupler to RJ45 – USB (942 096-001).

Technical Specifications

Product description

Type:	Adapter Cable RJ11/RJ45
Part Number:	942261001
Cable Length:	15 cm

Ambient conditions

Operating temperature:	0-+60 °C
Minimum Storage Temperature:	-20-+80 °C
Relative humidity (non-condensing):	10-95 %

Mechanical construction

Weight:	15 g
---------	------

Reliability

Guarantee:	24 months (please refer to the <a href="https://assets.belden.com/m/1424ddb7a3280e7a/original/Hirschmann-Automation-and-Control-GmbH-Terms-of-Guarantee.pdf" terms of guarantee </a for detailed information)
------------	---

Scope of delivery and accessories

Scope of delivery:	Cable
--------------------	-------

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.90 Revision Date: 11-27-2025
----------------------	---

Variants

Item #	Type	Cable Length
942261001	ADAPTER Cable RJ11/RJ45	15 cm

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.