Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	

APPROVED: _____

DATE: _____ TITLE: _____







基本尺寸	公差等级									
	1	2	3	4	5	6	7	8	9	10
	公差数值									
>280~315	0.20	0.28	0.38	0.55	0.74	1.1	1.4	2.2	2.8	4.4
>315~355	0.22	0.30	0.42	0.60	0.82	1.2	1.6	2.4	3.2	4.8
>355~400	0.24	0.34	0.46	0.65	0.90	1.3	1.8	2.6	3.6	5.2
>400~450	0.26	0.38	0.52	0.70	1.0	1.4	2.0	2.8	4.0	5.6
>450~500	0.30	0.42	0.60	0.80	1.1	1.6	2.2	3.2	4.4	6.4
>500~560	0.34	0.46	0.64	0.88	1.2	1.8	2.4	3.6	4.8	7.1
>560~630	0.38	0.52	0.72	0.99	1.3	2.0	2.7	3.9	5.4	7.9
>630~710	0.42	0.60	0.80	1.1	1.5	2.2	3.0	4.4	6.0	8.8
>710~800	0.46	0.64	0.90	1.2	1.7	2.5	3.3	4.9	6.7	9.8
>800~900	0.52	0.72	1.0	1.4	1.9	2.8	3.8	5.5	7.5	10.8
>900~1000	0.60	0.80	1.2	1.6	2.2	3.2	4.3	6.0	8.5	12.8
>1000~2000	0.76	1.0	1.4	1.8	2.5	3.5	5	7	10	14
>1200~1400	0.88	1.2	1.6	2.5	3.0	4.0	6	8	11	16
>1400~1600	1.0	1.4	1.8	3.0	3.5	5.0	7	9	13	18

注：表中公差数值用于基准孔或非配合孔时取正(+)号；用于基准轴或非配合轴取负(-)号，用于非配合长度取半值冠以正负(±)号。

SPECIFICATIONS:
Material:
Housing: V-0, Black
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

SEE CHART

APPROVALS		DATE
DRAWN	AY	11/27/18
CHECKED	AC	11/27/18
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
2*8P, AUTOMOBILE, PITCH 4.20, L=17.0/7.0

SIZE	PART NO.	REV.
X	ADT-AMMC3722PPCT001	-

REF: S00111C | SCALE: NTS | SHEET 1 OF 1