

ZCKE06

Limit switch head, Limit switches XC Standard,
ZCKE, cat's whisker



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product Compatibility	XCKJ
Associated body	ZCKJ5H7 ZCKJD39 ZCKJ2 ZCKJD39H29 ZCKJ5H29 ZCKJ1 ZCKJ11H7 ZCKJ6H29 ZCKJ21 ZCKJD37H29 ZCKJ1H7 ZCKJ5 ZCKJ21H29 ZCKJ9 ZCKJ9H29 ZCKJ6H7 ZCKJ9H7 ZCKJD35 ZCKJD39H7 ZCKJD31 ZCKJ2H29 ZCKJD37 ZCKJD37H7 ZCKJ21H7 ZCKJ8H7 ZCKJ8 ZCKJ7H7 ZCKJD31H7 ZCKJ11 ZCKJ8H29 ZCKJ7 ZCKJD35H29 ZCKJ11H29 ZCKJD31H29 ZCKJ2H7 ZCKJ1H29 ZCKJ7H29 ZCKJ6 ZCKJD35H7
Movement of operating head	Multi-directional
Type of operator	Cat's whisker spring return
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646238
Nbr. of units in pkg.	1
Package weight(Lbs)	4.37 oz (124.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.54 in (3.9 cm)
Package 1 width	1.54 in (3.9 cm)
Package 1 Length	6.54 in (16.6 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	18
Package 2 Weight	5.32 lb(US) (2.413 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	576
Package 3 Weight	187.87 lb(US) (85.216 kg)
Package 3 Height	29.53 in (75 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------