



MODEL: TS-KIT-01 | DESCRIPTION: TACTILE SWITCH KIT

FEATURES

- SPST circuit
- IP rated
- illuminated



MODELS

	QTY	illumination	actuator height	operating force	dimension	IP rating
			[mm]	[gf]	[mm]	
TS01-66-73-160-BK-D	5	NO	7.3	160 ± 50	6 x 6 x 7.3	---
TS02-66-73-BK-160-LCR-D	5	NO	7.3	160 ± 50	6 x 6 x 7.3	---
TS03-66-50-BK-160-LCR-D-67	5	NO	5	160 ± 50	6 x 6 x 5	IP67
TS04-66-43-BK-160-SMT-TR	5	NO	4.3	160 ± 50	6 x 6 x 4.3	---
TS05-66-43-BK-260-SMT-67	5	NO	4.3	260 ± 50	6 x 6 x 4.3	IP67
TS06-667-43-BK-160-G-SMT-TR	5	NO	4.3	160 ± 50	6 x 6.7 x 4.3	---
TS07-667-43-BK-160-SMT-TR	5	NO	4.3	160 ± 50	6 x 6.7 x 4.3	---
TS08-66-43-160-SMT-67	5	NO	4.3	160 ± 50	6 x 6 x 4.3	---
TS09-63-25-WT-160-SMT-TR	5	NO	2.5	160 ± 50	6.1 x 3.7 x 2.5	---
TS10-63-26-BE-250-SMT-TR	5	NO	2.6	250 ± 50	3.1 x 3.8 x 26	---
TS11-674-65-BK-100-RA-D	5	NO	6.5	100 ± 30	6 x 6.7 x 6.5	---
TS12-74-50-BK-250-SMT-TR	5	NO	5	160 ± 30[Center gf 250]	7.4 x 7.4 x 5	---
TS13-1212-73-BK-100-D	3	NO	7.3	100 ± 30	12 x 12 x 7.3	---
TS14-1212-150-BK-100-SCR-D	3	NO	15	100 ± 30	12 x 12 x 15	---
TS15-1212-50-BK-160-SCR-D	3	NO	5	160 ± 50	12 x 12 x 5	---
TS16-1212-85-BK-100-SMT-TR	3	NO	8.5	100 ± 30	12 x 12 x 8.5	---
TS17-48-05-YE-160-SMT-TR	10	NO	0.5	160 ± 50	4.8 x 4.8 x 0.5	---
TS18-5-15-SL-160-SMT-TR	10	NO	1.5	160 ± 50	5 x 5 x 1.5	---
TS20-42-25-WT-160-SMT-TR	10	NO	2.5	160 ± 50	4.2 x 3.2 x 2.5	---
TS21-34-035-BK-160-SMT-TR	10	NO	0.35	160 ± 50	3.4 x 3.4 x 1.5	---
TS22-45-035-BK-160-SMT-TR	10	NO	0.35	160 ± 50	4.8 x 4.8 x 1.7	---
TS23-46-06-BK-260-SMT-TR	10	NO	0.6	260 ± 50	3.5 x 3 x 1.4	---
TS24-62-14-BL-200-SMT-TR-67	5	NO	1.4	200 ± 30	6.2 x 6.2 x 5.4	IP67
TS26-68-25-BL-260-SMT-TR	5	YES	2.5	260 ± 50	7.2 x 6.8 x 7	---
TS27-68-24-BL-260-D & TS27-CAP	3	YES	7.2	260 ± 50	6 x 6 x 7.2	---
TS28-63-63-G-260-RA-D	3	YES	12.2	260 ± 50	6.8 x 6.3 x 12.2	---
TS29-1212-1-BL-300-D	3	YES	7.3	300 ± 100	12 x 12 x 7.3	---

MODELS (CONTINUED)

	QTY	illumination	actuator height	operating force	dimension	IP rating
			[mm]	[gf]	[mm]	
TS29-1212-1-G-300-D	3	YES	7.3	300 ± 100	12 x 12 x 7.3	---
TS29-1212-1-Y-300-D	3	YES	7.3	300 ± 100	12 x 12 x 7.3	---
TS30-46-35-BK-160-RA-SMT-TR	10	NO	1.85	160 ± 50	3.4 x 2.4 x 1.85	---
TS31-46-35-BK-B-160-RA-SMT-TR	10	NO	2.3	160 ± 50	4.6 x 1.8 x 2.3	---
TS32-7-35-BK-160-RA-SMT-TR	10	NO	3.6	160 ± 50	7 x 3.5 x 3.6	---
TS33-46-35-BK-160-SMT-TR	10	NO	3.5	160 ± 50	4.6 x 1.8 x 3.5	---
TS34-62-25-BK-G-100-SMT-TR	5	NO	2.5	100 ± 50	6.2 x 6.2 x 2.5	---
TS35-6-15-BK-160-JSMT-TR	10	NO	5	160 ± 50	6 x 6 x 5	---
TS36-62-31-BK-260-SMT-TR-67	10	NO	3.1	260 ± 70	6.2 x 7 x 3.1	IP67

IP RATING

IP RATING CHART		
IP LEVEL	First Digit: Ingress of solid objects	Second Digit: Ingress of liquids
0	No protection	No protection
1	Protected against solid objects over 50 mm e.g. hands, large tools.	Protected against vertically falling drops of water or condensation.
2	Protected against solid objects over 12.5 mm e.g. hands, large tools.	Protected against falling drops of water, if the case is disposed up to 15° from vertical.
3	Protected against solid objects over 2.5 mm e.g. wire, small tools.	Protected against sprays of water from any direction, even if the case is disposed up to 60° from vertical.
4	Protected against solid objects over 1.0 mm e.g. wires.	Protected against splash water from any direction.
5	Limited protection against dust ingress. (no harmful deposit)	Protected against low pressure water jets from any direction. Limited ingress permitted.
6	Totally protected against dust ingress.	Protected against high pressure water jets from any direction. Limited ingress permitted.
7	N/A	Protected against short periods of immersion in water.
8	N/A	Protected against long, durable periods of immersion in water.
9k	N/A	Protected against close-range high pressure, high temperature spray downs.

REVISION HISTORY

rev.	description	date
1.0	initial release	12/15/2025

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com