

N Male to Straight Cut Lead Cable RG-214 Coax in 36 Inch

The 50 ohm type N male to straight cut lead 36 inch cable using RG-214 coax, part number FMC0100214-36, from Fairview Microwave is in-stock and ships same day. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness. These N Male to unterminated flush cut cables assemblies are designed to be used as convenient test probes.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Diameter	0.787 in [19.99 mm]

Cable

Cable Type	RG-214
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.425 in [10.8 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	Straight Cut Lead
Configuration	Straight	Straight
Impedance	50 Ohms	0 Ohms
Contact Material & Plating	Brass, Gold	
Dielectric Type	PTFE	
Body Material & Plating	Brass, Nickel	

Environmental Specifications

Temperature

Operating Range	-25 to +70 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Configuration:

- N Male
- Straight Cut Lead
- RG-214

Features:

- Double Shielded
- PVC Jacket

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

How to Order

Part Number Configuration:

FMC0100214 - xx uu

_____ cm = Centimeters
_____ <blank> = Inches
_____ Length


Example: FMC0100214-12 = 12 inches long cable
FMC0100214-100cm = 100 cm long cable

N Male to Straight Cut Lead Cable RG-214 Coax in 36 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [N Male to Straight Cut Lead Cable RG-214 Coax in 36 Inch FMC0100214-36](#)

URL: <https://www.fairviewmicrowave.com/n-male-sexless-cable-rg214-coax-fmc0100214-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC.

WWW.FAIRVIEWMICROWAVE.COM

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

N Male to Straight Cut Lead Cable RG-214 Coax in 36
Inch

DWG NO

FMC0100214

CAGE CODE

3FKR5

CAD FILE

101014

SHEET

SCALE

N/A

SIZE

A

5568