Qi2.2 Certified 25W Magnetic Wireless Charging Pad with 6.6ft (2m) USB-C Tethered Cable, MagSafe Compatible for iPhone 18/17/16 Pro/Pro Max, iPhone Duo, Black

Product ID: 1PB-WIRELESS-CHARGER



This Qi2.2 25W Wireless Charger delivers fast, reliable wireless charging for smartphones, combining broad compatibility with a simple, clutter-free design. With a 6.6ft/2m USB-C cable and support for multiple Qi power profiles, it provides flexible charging for home, office, or travel setups.

The Qi2.2 Certified charger delivers up to 25W of power for phones and has backward compatibility for 5W, 7.5W, 10W, and 15W devices. For optimal performance, use a 30W USB-C PD charger; lower wattage PD chargers will affect maximum wireless charging output. The long cable offers convenient placement on your desk, counter, or side table.

Designed for MagSafe-enabled iPhones including iPhone Duo, iPhone 18 Pro/Pro Max, iPhone 17 Pro/Pro Max and iPhone 16 Pro/Pro Max, this phone charging pad also supports devices like Google Pixel 10 (with Pixelsnap) and non-magnetic smartphones such as Samsung S26/S26 Ultra with manual alignment required.

Built for dependable performance, this Qi2.2 certified charger includes over-current and over-temperature protection to safeguard your device during charging.

The product ships in 100% plastic free, FSC Mix packaging made from responsibly sourced materials. This aligns your IT infrastructure with your organization's sustainability goals, without compromising on quality or durability.

Certifications, Reports and Compatibility

Applications

• Enable fast wireless charging in shared desks or reception areas, reducing cable clutter while supporting MagSafe and Qi2.2 devices

• Provide simple charging for home, office, or travel setups with flexible placement and multi-level Qi2.2 support

Features

• Effortless 25W Magnetic Wireless Charging: Snap your device into place for fast, reliable Qi2.2 charging up to 25W w/ precise magnetic alignment; 6.6ft (2m) tethered cable connects to dock, laptop, or USB-C charger (min. 30W USB-C PD for peak performance)

• Works Across iPhone, Pixel, and More: MagSafe compatible for iPhone Duo, iPhone 18/17/16 Pro / Pro Max; Also supports Google Pixel 11/10 Pixelsnap and non-magnetic phones like Samsung S26 / S26 Ultra using manual alignment or a magnetic case

• Qi2.2 Certified for Safe, Reliable Charging: Qi2.2 certified phone charging pad provides up to 25W and supports Qi 5W 7.5W 10W 15W profiles with built-in over-current and over-temperature protection to safeguard your mobile device/smart phone during use

• Reduce Packaging Waste: This product features 100% plastic free FSCMix certified packaging; Compact packaging protects the product in transit while minimizing environmental impact

• The IT Pro's Choice: Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

General		
	UPC	065030919890
	Warranty	2 Years
Power		
	Input Voltage	5V, 9V, 12V, 15V
	Plug Type	USB-C
Physical & Environmental		
	Color	Black
	Cable Length	6.6 ft [2 m]
	Product Length	2.0 in [51 mm]
	Product Width	2.0 in [51 mm]
	Product Height	0.3 in [8.6 mm]

	Weight of Product	4.4 oz [125 g]
	Operating Temperature	0C to 35C (32F to 95F)
	Storage Temperature	-20C to 80C (-4F to 176F)
	Humidity	10% ~ 90%
Packaging & In-the-Box		
	Included in Package	1 - Wireless Charging Pad
	Package Width	6.7 in [17 cm]
	Package Depth	5.6 in [14.2 cm]
	Package Height	1.2 in [30 mm]
	Shipping (Package) Weight	4.8 oz [135 g]

Product appearance and specifications are subject to change without notice.