

Desk Mount Dual Monitor Arm with USB & Audio - Slim Full Motion Adjustable Dual Monitor VESA Mount for up to 32" (17.6lb/8kg) Displays - Ergonomic Articulating - C-Clamp/Grommet

Product ID: ARMSLIMDUAL2USB3



This desk mount dual monitor arm lets you mount two 17" to 32" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable crossbar design, the dual computer screen stand lets you create more usable work-space by mounting your monitors side by side on a single base. The ergonomic monitor mount features a flat low-profile back that lets you position your displays against a wall or cubicle wall. The built-in USB 3.0 ports at the base provide a convenient way to connect your peripherals.

The multi monitor mount features one -touch height adjustment. The smooth +/- 10° tilt motion and +/- 10° swivel make it easy to find the optimal viewing angle. You can also rotate each display 360° for portrait or landscape viewing and keep your displays at the same height with the horizontal crossbar.

The VESA dual monitor mount is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ARMSLIMDUAL2USB3 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal in office applications including shared workstations with multiple users
- Rotate your display from landscape to portrait position for web design or coding

Features

- 32 INCH HEAVY DUTY MONITOR MOUNT: VESA 75x75/100x100mm compatible multi monitor mount supports two displays up to 32" (17.6 lb/8 kg) per screen w/ 2 USB 3.0 passthrough ports & 2 3.5mm audio/mic jacks
- ONE-TOUCH ADJUSTMENT: Max height of 23.4" from the desk, the spring-assisted monitor arm with a sturdy handle offers toolless adjustable height range of 13" and can extend outwards up to 23" from base
- WIDE RANGE OF MOTION: Articulating ergonomic arm increases comfort & productivity w/ individual monitor +/-10 tilt, +/-10 swivel, 360 rotating arm & sliding horizontal crossbar for screen alignment
- CONVENIENT CONNECTIVITY: Desk mount dual monitor arm incl. 2 USB-A 3.1 Gen 1 5Gbps & 2 3.5mm ports that extend your PC/laptop/computer/dock ports for connecting devices & has built-in cable management
- EASY INSTALLATION: C-clamp or grommet mount to secure to desktop (10 mm-85 mm); detachable VESA plate w/ quick release clip makes mounting displays easy; tools incl. to adjust articulation tension

Hardware

Warranty	2 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.35 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 1.89 in. (10 - 48 mm)

Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	17"
Maximum Display Size	32"
Height Adjustment	Yes
Display Tilt	+10 / -10
Display Swivel	+10 / -10
Swivel / Pivot	+/- 90 at the crossbar +/- 180 at the shoulder +/- 180 at the elbow
Display Rotation	360

Physical Characteristics

Color	Black
Construction Material	Aluminum
Product Length	28.5 in [725.0 mm]
Product Width	32.7 in [83.0 cm]
Product Height	29.9 in [76.0 cm]
Weight of Product	257.7 oz [7300.0 g]

Packaging Information

Package Quantity	1
Package Length	9.1 in [23.0 cm]
Package Width	35.4 in [90.0 cm]
Package Height	6.2 in [15.7 cm]
Shipping (Package) Weight	19.7 lb [8.9 kg]

What's in the Box

Included in Package	1 - Base Clamp Assembly
---------------------	-------------------------

- 1 - Lower Arm
- 1 - Upper Arm
- 1 - Cross Bar
- 2 - VESA Mount
- 1 - Grab Handle
- 1 - Grommet Plate
- 1 - Base Plate
- 1 - Adhesive Foam Pad
- 1 - Cable Management Clip, Base
- 4 - Button Head Hex Screws
- 2 - Flat Head Hex Screws
- 1 - 3mm Hex Key
- 1 - 4mm Hex Key
- 1 - 6mm Hex Key
- 8 - M4 x 12 Screws
- 8 - M5 x 12 Screws
- 8 - Washers
- 4 - Countersunk Hex Screws
- 1 - Grommet Screw
- 1 - Upper C Clamp Bracket
- 1 - Lower C Clamp Assembly

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*