

2U Server Rack Shelf - Universal Vented Rack Mount Cantilever Tray for 19" Network Equipment Rack & Cabinet - Heavy Duty Steel – Weight Capacity 50lb/23kg - 22" Deep Shelf, Black

**Product ID:** CAB SHELF22V



The CAB SHELF22V 2U 22in Depth Vented Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options.

Our vented rack shelves improve air flow and help to lower temperatures in the rack. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

## Certifications, Reports and Compatibility

## Applications

- Supply additional storage space for mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

## Features

- **UNIVERSAL 19" FIT:** This 2U vented server rack mount shelf is designed to fit virtually any 19in server rack and can accommodate an internal depth of 22in (56cm) for your data, IT, networking, or other non-rack mount equipment
- **MAXIMIZE VENTILATION:** The vented shelf plate on the cantilever rack shelf ensures consistent airflow to

effectively dissipate heat on servers; it also works great to keep your computer and AV equipment cool in your home, studio, or office space

- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures long term durability and supports a total weight of 50lbs/23kg making it the perfect rack shelf solution for any environment
- **VERSATILE FUNCTIONALITY:** At 22in deep, this fixed rack mount shelf is designed to work with any 19in cabinet or equipment rack; it provides additional storage space for mission critical hardware, and can even store your tools or audio / video accessories
- **INDUSTRY-LEADING SUPPORT:** 2U vented server rack mount shelf is backed for life, including free lifetime 24/5 technical assistance

---

#### Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Industry Standards	EIA/ECA-310-E
Mounting Options	Front Mount (Front Only)

---

#### Performance

Weight Capacity (Stationary)	50.7 lb [23 kg]
------------------------------	-----------------

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	22.0 in [55.9 cm]
Product Width	19.0 in [48.3 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	6.3 lb [2.8 kg]

---

#### Packaging Information

Package Quantity	1
------------------	---

---

Package Length	21.7 in [55.2 cm]
Package Width	24.8 in [63.1 cm]
Package Height	6.7 in [16.9 cm]
Shipping (Package) Weight	8.9 lb [4.0 kg]

---

#### What's in the Box

Included in Package	1 - 2U 22in Depth Rack Shelf  4 - M6 Screws  4 - M6 Cage Nuts  4 - M6 Plastic Washers  1 - Instruction Manual
---------------------	---

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***

