

Solid Cable Management Raceway with Cover, 2"(50mm)W x 3/4"(20mm)H - 6.5ft(2m) length, 3 Compartment Network Cable Hider - Wire Duct System, Power Cord Concealer, UL Listed - TAA

Product ID: CBMCWD5020



This 6.5 ft. (2 m) cable management raceway neatly routes cables in your office or server room, while also concealing them to create a tidy and professional look.

This cable management raceway protects cables from damage while neatly routing them in your office or server room. The raceway is 0.8 in. (20 mm) x 2 in. (51 mm) with three individual channels running throughout the raceway you can use to easily organize and separate cables.

Made from self extinguishing PVC, that's sturdy and warp proof this network/power cable hider/concealer is M1 Rating NF fire resistant with a 186F (86C) Vicat softening point and are UL/94V-0 Rated.

The cable raceway can be mounting by simply drilling holes through housing and into any surface, or double sided tape can be used to secure the raceway (screws and tape not included).

To combine and route this cable management raceway and cap ends for a professional finish, StarTech.com offers a wide selection of raceway accessories.

The End Piece (CBMCWD5020E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMCWD5020I) (20-Pack), joins two raceways together inside of corners at a 90 degree angle.

The Outside Elbow (CBMCWD5020O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

Certifications, Reports and Compatibility



Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- PROFESSIONALLY ORGANIZE & ROUTE CABLES: Cable management raceway protects cables from damage & neatly routes them in your office or server room; Features 3 channels to easily organize multiple cables
- INDUSTRIAL STRENGTH: Made from sturdy warp-proof, self extinguishing PVC, this network/power cable hider/concealer is M1 Rating NF fire resistant w/ 186F (86C) Vicat softening point; UL/94V-0 Rated
- RACEWAY ACCESSORIES: End Piece (CBMCWD5020E), Inside Elbow (CBMCWD5020I), Outside Elbow (CBMCWD5020O); sold separately
- TECHNICAL SPECIFICATIONS: Length: 6.5ft (2m) Height: 0.8" (20mm) Total Width: 2" (51mm) Cable/Wire Channel Widths: Left 0.6" (15mm), Center 0.4" (11mm), Right 0.6" (15mm) White RoHS
- STARTECH.COM ADVANTAGE: IT professional's choice for over 30 years; This surface mount cord cover kit/wiring duct system is backed for 2 years by StarTech.com, including free 24/5 tech support

Performance

Warranty	2 Years
General Specifications	Left Channel Width: 0.6 in [14.8 mm]
	Center Channel Width: 0.4 in [10 mm]
	Right Channel Width: 0.6 in [14.8 mm]

Physical Characteristics

Color	White
Material	PVC
Product Length	2.0 in [5.1 cm]
Product Width	78.7 in [200.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	1.9 lb [0.9 kg]

Packaging Information

Package Quantity	1
------------------	---

Package Length	2.0 in [5.1 cm]
Package Width	6.6 ft [2.0 m]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	2.0 lb [0.9 kg]

What's in the Box

Included in Package	1 - Raceway
---------------------	-------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

