

100 Pack Cable Clips with Nails - Two Steel Nails - Reusable Nail-in Clamps - Brick/Drywall Cable Fasteners - Ethernet Cord/AV/Coax Cable - Mounting Cable Tacks - White - TAA

Product ID: CBMDNMCC1



These double nail cable clips secure cables to the wall to route and organize them. 100 White cable clips are included, ensuring you'll have plenty on hand.

These cable clips with two steel nails enable you to route cables while mounting them to a wall or ceiling. They feature internal dimensions of 0.49 in. (12.5 mm) x 0.31 in. (8 mm). They're quick and easy to install, remove and reuse, with two 0.07 in. x 1.22 in (1.78 mm x 31 mm) steel nails included that secure the bundle and mounts it to the wall -- perfect for organizing and routing network cables, power cables, electrical cables or other cables at your home or office.

Made of durable PE material and featuring 2-galvanized iron nails these cable clips ensure a strong bearing capacity and are corrosion resistant and suitable for securing cable bundles to wood, drywall, and masonry.

To suit different applications, StarTech.com offers a variety of single and double nail cable clips:

Medium Single Steel Nail Cable Clips - 100 Pack (CBMNMCC2)

Large Single Steel Nail Cable Clips - 100 Pack (CBMNMCC3)

Extra Large Single Steel Nail Cable Clips - 100 Pack (CBMNMCC4)

Medium Double Steel Nail Cable Clips - 100 Pack (CBMDNMCC1)

Large Double Steel Nail Cable Clips - 100 Pack (CBMDNMCC2)

These cable clips are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Route cables while mounting them to a wall or ceiling in your office or server room

Features

- 100 PACK OF CABLE CLIPS WITH NAILS: Nail-in cable clips w/ internal dimensions of 12.5 mm x 8 mm (0.49" x 0.31") keep cables organized; Install & reuse w/ 2 steel nails 1.78 mm x 31mm (0.07" x 1.22")
- HIGH-QUALITY: Clamps made w/durable PE material & feature steel nails to ensure easy installation and resuability/long life; 2-steel nails ensure a strong bearing capacity & corrosion resistance; TAA
- REDUCE CLUTTER: Secure coax cable, RJ11 telephone wire, audio, video, RJ45 CAT5/CAT6 network & USB cables to baseboards & wood trim to reduce clutter; Suitable for wood, drywall & brick wall surfaces
- MULTI-LENGTH: Large size also available (CBMDNMCC2) with internal dimensions of 18.7 mm x 8.0 mm (0.74" x 0.31") & steel nail size 1.86 mm x 31mm (0.07" x 1.22") White Plastic (PE) Material
- THE STARTECH.COM ADVANTAGE: StarTech.com offers free lifetime warranty & 24/5 multilingual technical support based in North America on these Ethernet cord mounting/cable wall fasteners/tacks

Performance

Warranty	2 Years
General Specifications	Nail Size: 0.07 in [1.86 mm] x 1.22 in [31 mm]
	Internal dimensions: 0.49 in [12.5 mm] x 0.31 in [8 mm]

Physical Characteristics

Color	White
Material	PE
Product Length	0.4 in [0.9 cm]
Product Width	0.9 in [2.2 cm]
Product Height	1.2 in [3.1 cm]
Weight of Product	0.1 oz [2.0 g]

Packaging

Information

Package Quantity	100
Package Length	5.1 in [12.9 cm]
Package Width	5.8 in [14.8 cm]
Package Height	1.8 in [4.5 cm]
Shipping (Package) Weight	7.5 oz [212.0 g]

What's in the Box

Included in Package	100 - Cable Clips
---------------------	-------------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

