

100 Pack Large Cable Clips with Nail - Reusable - Nail-in Clamps - Wire Holding Clips - Ethernet Cord/AV/Coax Cable Fasteners - Brick/Drywall Mounting Cable Tacks - White - TAA

**Product ID:** CBMNMCC3



These single nail cable clips secure cables to the wall to route and organize them. 100 White cable clips are included, ensuring you'll have plenty on hand.

#### Secure Your Cables with an Included Steel Nail

These electrical cable clips with steel nail enable you to route cables while mounting them to a wall. They hold cables from 0.28 in. (7 mm) to 0.39 in. (10 mm) in diameter. They're quick and easy to install, remove and reuse, with a .06 in. x 0.98 in. (1.6 mm x 25 mm) steel nail included that secures and mounts it to the wall -- perfect for organizing and routing network cables, power cables, or other cables at your home or office.

#### Industrial Strength

Made of durable PE material and featuring a galvanized steel nail, these cable clips ensure a strong bearing capacity and are corrosion resistance and suitable for securing cables to wood, drywall and masonry.

#### Available in Different Sizes

To suite different application, StarTech.com offers a variety of single and double nail cable clips:

Medium Single Steel Nail Cable Clips - 100 Pack (CBMNMCC2)

Large Single Steel Nail Cable Clips - 100 Pack (CBMNMCC3)

Extra Large Single Steel Nail Cable Clips - 100 Pack (CBMNMCC4)

Medium Double Steel Nail Cable Clips - 100 Pack (CBMDNMCC1)

Large Double Steel Nail Cable Clips - 100 Pack (CBMDNMCC2)

These cable clips are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical

support. StarTech.com has been the IT professionals choice for over 30 years.

## Certifications, Reports and Compatibility



## Applications

- Route cables while mounting them to a wall or ceiling in your office or server room

## Features

- 100 PACK OF CABLE CLIPS WITH NAIL : Clamps holds cables from 0.28-0.39in (7-10mm) in diameter, keeping cables organized; Install & reuse w/ a steel nail .06x0.98" (1.6 mmx25 mm)
- HIGH-QUALITY: Cord mounting fasteners made w/durable PE material with a steel nail to ensure resuability/long life; steel nail ensures easy installation, bearing capacity & corrosion resistance; TAA
- REDUCE CLUTTER: Secure coax cable, RJ11 telephone, audio, video, RJ45 CAT5/CAT6 Ethernet network & USB cables to baseboards & wood trim to reduce clutter; suitable for wood, brick/drywall & masonry
- AVAILABLE IN OTHER SIZES: Medium (CBMDNMCC2) holds cables from 0.20-0.28in (5-7mm) w/0.06x0.98" (1.6x25mm) nail; Extra-Large (CBMNMCC4) holds cables from 0.39-0.55" (10-14mm) w/0.08x1.18" (2x30mm) nail
- STARTECH.COM ADVANTAGE: These white reusable wire holding tacks are backed for life by StarTech.com, including 24/5 technical support

---

### Physical Characteristics

Warranty	2 Years
Color	White
Material	PE
Product Length	0.4 in [0.9 cm]
Product Width	0.5 in [1.2 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	0.0 oz [0.8 g]

---

### Packaging

**Information**

Package Quantity	100
Package Length	4.5 in [11.4 cm]
Package Width	4.4 in [11.3 cm]
Package Height	1.1 in [2.7 cm]
Shipping (Package) Weight	3.0 oz [86.0 g]

---

**What's in the Box**

Included in Package	100 - Cable Clips
---------------------	-------------------

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

