


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/09/2023	HBAKKE	PHOSPODAR



ITEM NUMBER	LENGTH	
	METERS	FEET
FCA-SCSC-DPLCV-01	1.0	3.28
FCA-SCSC-DPLCV-05	5.0	16.40

NOTES:

1. CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-COM TM an INFINIT [®] brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE: $\pm 12 [305] = +1 [25] / -0$ >math>\pm 12 [305] = +1 [25] / -0</math> $\pm 60 [1524] = +2 [51] / -0$ >math>\pm 60 [1524] = +2 [51] / -0</math> $\pm 120 [3048] = +4 [102] / -0$ >math>\pm 120 [3048] = +4 [102] / -0</math> $\pm 300 [7620] = +6 [52] / -0$ >math>\pm 300 [7620] = +6 [52] / -0</math> $\pm 300 [7620] = +5\% / -0$	DRAWN BY HBAKKE	08/09/2023		
CHECKED BY DMAY	08/09/2023			
APPROVED BY TCAHALANE	08/09/2023			
UNIVERSAL THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	FIBER OPTIC PATCH CABLE SC/PC-SC/PC DUPLEX 100/140 LARGE CORE MULTIMODE FIBER 3.0MM PVC	
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. FCA-SCSC-DPLCV
		REV. A		
	SCALE: NONE	CAD FILE: FCA-SCSC-DPLCV.SLDDRW		SHEET 1 OF 1