

FTTH Terminal Box 2 Ports with 2 LC/APC SM Duplex Adapter and 4 LC/APC SM Pigtails



LCFTB-E-LCA

Features

- Low profile Fiber to the Home (FTTH) design
- 2 LC/APC duplex couplers & 4 SM 0.9mm pigtails included
- ABS plastic indoor wall mount
- Cable in/out ports: 1 inlet, 2 outlet

Applications

- FTTH Access Networks
- Small office/home office (SOHO) networks
- Metropolitan area networks (MANs)
- CATV Networks

Description

The L-com LCFTB-E-LCA FTTH Terminal Box presents a cutting-edge solution for indoor fiber optic termination and distribution of optical cables. Crafted with sturdy ABS plastic, this wall-mountable box guarantees durability and reliability for your network connections. Featuring 1 inlet, 2 outlet, it facilitates seamless connectivity, ensuring smooth data transmission throughout your infrastructure.

L-com's LCFTB-E-LCA FTTH Fiber Information Panel comes fully equipped with 2 LC/APC duplex couplers and 4 SM 0.9mm pigtails, making it ready for splicing and immediate deployment. Its low-profile design makes it ideal for Fiber to the Home (FTTH) setups, effortlessly blending into any indoor environment without occupying unnecessary space. With its compact yet robust construction, this fiber optic FTTH Fiber Information Panel offers the perfect housing solution for your fiber optic network, ensuring both protection and accessibility.

Engineered for efficiency, the L-com LCFTB-E-LCA streamlines fiber optic management with its convenient cable in/out ports. Whether you are establishing a new network or upgrading an existing one, this indoor provides the reliability and functionality needed for seamless operation. Invest in the L-com LCFTB-E-LCA for a hassle-free solution that meets the demands of modern fiber optic FTTH termination connectivity, ensuring optimal performance for your network infrastructure.

Configuration

Number of Ports Connector 1	2
-----------------------------	---

Mechanical Specifications

Size		
Outer Height	3.9 in	[99.06 mm]
Outer Width	3.2 in	[81.28 mm]
Outer Depth	0.9 in	[22.86 mm]
Weight	0.2 lbs	[90.72 g]
Enclosure Material	ABS Plastic	

Environmental Specifications

Operating Temperature	-40 to 60 deg C
-----------------------	-----------------

FTTH Terminal Box 2 Ports with 2 LC/APC SM Duplex Adapter and 4 LC/APC SM Pigtails from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/ftth-terminal-box-2-ports-2-lc-apc-sm-duplex-adapter-4-lc-apc-sm-pigtails-lcftb-e-lca-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCFTB-E-LCA CAD Drawing

FTTH Terminal Box 2 Ports with 2 LC/APC SM Duplex Adapter and 4 LC/APC SM Pigtailed

