

10ft (3m) DisplayPort to DVI Cable - DisplayPort to DVI Adapter Cable 1080p Video - DisplayPort to DVI-D Cable Single Link - DP to DVI Monitor Cable - DP 1.2 to DVI Converter

**Product ID:** DP2DVIMM10



The DP2DVIMM10 DisplayPort to DVI (M-M) Video Converter Cable lets you connect a DVI capable display to a DisplayPort video card/source using a single cable. The cable provides a connection distance of 10ft and features a male DVI connector and a male DisplayPort connector.

The DisplayPort/DVI video converter cable supports high bandwidth video transmissions, easily delivering monitor resolutions up to 1920x1200 or HDTV resolutions up to 1080p - allowing you to take full advantage of your DVI capable display, while using a cutting edge DisplayPort video source.

DP2DVIMM10 is a passive adapter cable that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Keep your existing DVI display with our DisplayPort to DVI video converter cables
- The DisplayPort to DVI cable allows for an easy and hassle free connection to any DVI-D (digital) display

## Features

- **DISPLAYPORT TO DVI CABLE:** 10ft (3m) DisplayPort 1.2 (HBR2) to DVI-D single-link cable connects a DVI display, monitor or projector supports 1920x1200 or 1080p at 60Hz; HDCP 1.3 EDID pass-through ensures compatibility between source & display
- **COMPATIBILITY:** Passive video converter supports DP++ sources including workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations; 10' length supports longer distances than traditional DVI cable
- **INTEGRATED DISPLAY CABLE:** DisplayPort to DVI adapter cable has slim/flexible design w/ adapter chip built into DVI connector reducing clutter & providing a tidy install in the office, boardroom or home office
- **STABLE CONNECTION:** Non-latching DP connector is easy to disconnect from a hard to reach source, and chip built into DVI connector minimizes signal loss. Supports DVI screw locking cable to prevent cable from coming loose or accidental disconnection
- **EASY TO USE:** With no software or drivers required, the DP to DVI cable/cord works with any OS including Windows, Ubuntu and macOS; DisplayPort male to DVI male cable

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

### Performance

Maximum Cable Length	10.0 ft [3.0 m]
Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

---

### Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DVI-D (25 pin)

---

### Special Notes /

**Requirements**

Note	DP++ (DisplayPort++) port required from video card or video source.
------	---

**Physical Characteristics**

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	8.7 oz [246.0 g]

**Packaging Information**

Package Quantity	1
Package Length	11.2 in [28.5 cm]
Package Width	13.6 in [34.6 cm]
Package Height	1.2 in [3.1 cm]
Shipping (Package) Weight	9.2 oz [260.0 g]

**What's in the Box**

Included in Package	1 - 10 ft DisplayPort to DVI Video Adapter Converter Cable - M/M
---------------------	--

**Warranty Information**

Warranty	3 Years
----------	---------

***\*Product appearance and specifications are subject to change without notice.***