


## 3m Fiber Optic Cable - Multimode Duplex 62.5/125 LSZH Fiber Jumper Cord - LC/ST

Product ID: FIBLCST3



The FIBLCST3 3-meter (10ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one ST (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-ST Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

### Certifications, Reports and Compatibility



### Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication

- Used by long distance networks with mission critical data

## Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

---

### Hardware

Warranty	Lifetime
Fiber Size	62.5/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM1

---

### Performance

Maximum Data Transfer Rate	10Gbps
Cable Rating	1Gbps / 10Gbps
Type	Multi Mode

---

### Connector(s)

Connector A	1 - Fiber Optic LC Duplex
Connector B	1 - Fiber Optic ST Duplex

---

### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~90% RH

---

### Physical Characteristics

Color	Orange
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]

---

Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [0.7 cm]
Weight of Product	1.8 oz [52.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	6.9 in [17.4 cm]
Package Width	6.6 in [16.8 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	2.2 oz [62.0 g]

---

**What's in the Box**

Included in Package	1 - 3m Multimode 62.5/125 Duplex Fiber Patch Cable LC – ST
---------------------	------------------------------------------------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***

