

## TV Ceiling Mount - Full-Motion Universal Hanging Single Screen Mount with Adjustable Telescopic Short Pole - Tilt / Swivel - VESA Bracket for 32"-75" Displays

**Product ID:** FPCEILPTBSP



This ceiling TV mount supports VESA mount compatible TVs from 32" to 75" in size, with a weight capacity of up to 110 lb. (50 kg). It lets you save wall and floor space by hanging your flat-panel LCD, LED or plasma TV from the ceiling in a prominent area.

The ceiling mount is ideal for use in corporate boardrooms, lobbies, entrances, restaurants, bars and meeting places.

With a telescopic pole, the TV mount lets you suspend a display at your desired distance from the ceiling. This works well with a range of ceiling heights. The steel pole can extend from 22" to 33.5" (560 to 910 mm), with a total lift (height extension) of 13.7" (350 mm).

The flat-screen ceiling mount accommodates a wide variety of ceiling types. You can swivel the TV to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees), and pitched or horizontal (flat) ceilings.

You can adjust your TV to create a comfortable viewing angle, by tilting it up to -25 degrees down towards your audience for optimum visibility. Plus, the full-motion mount lets you swivel your display around the pole + 180 / - 180 degrees, without using tools.

Simply attach the included vertical brackets, with built-in hooks, to the back of your TV. Once attached, hang your TV securely onto the ceiling mount. The +/-3 degree post-installation leveling adjustments ensure ideal positioning after hanging.

FPCEILPTBSP is backed by a StarTech.com 5-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



## Applications

- Suspend a flat-screen TV from the ceiling for easy viewing
- Ideal for boardrooms, lobbies, entrances, meeting spaces, classrooms
- Keep your guests informed and entertained

## Features

- **SINGLE 75" TV CEILING MOUNT:** VESA compatible ceiling mount supports displays up to 75" (110lb/50kg) including curved TVs; Height adjustable pole, 22.0" - 35.8" (56cm - 91cm) from ceiling
- **FULL MOTION:** Ceiling TV mount allows for the display to be swiveled 180 around the telescopic pole, and tilt downwards -25 degrees, without using tools
- **VERSATILE INSTALLATION:** Adjustable mounted ceiling bracket for TV / screen allows the pole to be adjusted and secured +/-60 degrees for angled/sloped/slanted ceilings to ensure displays are level
- **COMPATIBILITY:** Universal hanging TV ceiling mount supports LG, Samsung, Sony, and Sharp TVs among others (screws/spacers incl) & VESA hole patterns of 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400
- **TIDY AESTHETIC:** The universal television ceiling mount for one large display provides a hook-and-mount design for easy setup and integrated cable management; ideal for digital signage applications

---

### Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
# of Displays Supported	1
Mounting Options	Ceiling Mount
VESA Hole Pattern(s)	200x200 mm
	200x400 mm
	200x300 mm
	300x200 mm

	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x200 mm
	600x300 mm
	600x400 mm
Mounting Surface Thickness	560 mm to 910 mm

---

## Performance

General Specifications	Post-Installation Leveling Adjustment: +/-3
Weight Capacity (Per Display)	110.2 lb [50 kg]
Minimum Display Size	32"
Maximum Display Size	75"
Fits Curved Display	Yes
Video Wall	No
Height Adjustment	Yes
Minimum Height	22.0 in [560 mm]
Maximum Height	35.8 in [910 mm]
Display Tilt	+0 / -25
Swivel / Pivot	+180 to -180
Display Rotation	360
Anti-theft	No

---

## Physical Characteristics

Color	Black
-------	-------

Material	Steel
Product Length	26.8 in [68.0 cm]
Product Width	17.1 in [43.5 cm]
Product Height	45.3 in [115.0 cm]
Weight of Product	10.8 lb [4.9 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	15.0 in [38.0 cm]
Package Width	30.6 in [77.6 cm]
Package Height	5.9 in [15.0 cm]
Shipping (Package) Weight	14.8 lb [6.7 kg]

---

**What's in the Box**

Included in Package	1 - ceiling mount and pole
	1 - extension pole
	2 - vertical brackets
	1 - horizontal bracket
	2 - bolts
	2 - nuts
	1 - wrench
	1 - hex key
	1 - mounting template
	4 - M5x14 mm screws
	4 - M6x14 mm screws
	4 - M6x30 mm screws
	4 - M8x30 mm screws

- 4 - M8x50 mm screws
- 4 - rectangular washers
- 8 - small spacers
- 8 - large spacers
- 4 - 6.3x55 mm screws
- 4 - concrete anchor
- 4 - circular washers
- 1 - instruction manual

---

**Warranty  
Information**

Warranty	5 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***