

Full Motion TV Wall Mount - 32-55 inch (77lb/35kg) VESA Displays - Low Profile Universal Flat Screen TV Wall Mount - Heavy Duty Adjustable Tilt/Swivel Articulating Arm Bracket

**Product ID:** FPWARTB1M



Maximize space while creating an impressive display. This full-motion TV wall mount, made of heavy-duty steel, securely supports flat-screen TVs from 32" to 55". The arm extends easily to provide smooth, full-motion positioning for ideal viewing.

Mount your flat-screen TV in a location that's convenient for visitors, clients and employees. This TV wall mount is ideal for the lobby, boardroom or other venues, providing an impressive and secure way to display a flat-panel TV or mount digital signage. It also frees up valuable space. The TV wall mount supports most 32" to 55" (558.8 to 1397 mm) LED or LCD flat panel TVs weighing up to 77 lb. (35 kg).

The TV wall mount provides full-motion adjustment capability. The arm extends up to 19.8" (503 mm) from the wall to provide a wide range of movement and accommodate different screen positions and angles. The arm can also fold to tuck-in closely to the wall, providing a minimized profile, which enables you to position your display just 1.9" (49 mm) from the wall.

The TV wall mount swivels +90 / -90 degrees to provide maximum viewing flexibility. The mount also tilts +2 / -12 degrees, letting you angle your TV display toward your audience. With the tilt feature, you can mount your TV lower or higher than eye level and still view it comfortably.

The robust steel design safely and securely supports your flat-screen TV, to protect your investment. The TV wall mount also includes plastic brackets for cable management to keep cables neatly out of sight.

The FPWARTB1M is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Securely wall-mount your TV for easy viewing in boardrooms, lobbies, classrooms and meeting spaces
- Keep guests informed in hotels, restaurants and other venues
- Save space by wall-mounting your TV in your home theater

## Features

- 55" TV WALL MOUNT: This heavy-duty TV wall mount supports VESA compatible displays incl. curved TVs up to 55 inch (77 lb/35 kg) w/ a durable full-motion steel frame and a powder-coated finish
- WIDE RANGE OF MOTION: Articulating & adjustable TV wall mount offers +/-90 swivel, +2/-12 tilting & +/-5 LCD screen level adjustment without the use of additional tools to ensure display is level
- EXTENDABLE ARM: Arm can extend from 1.9" (49mm) to 19.8" (503mm) from the wall; With the length of the arm, center of the display has an overall lateral range (left to right) of 39.6" (1006mm)
- COMPATIBILITY: Universal television wall mount supports LG, Samsung, & others (screws/spacers incl) & VESA hole patterns 100x100, 100x150, 200x100, 200x200, 300x200, 300x300, 400x200, 400x300, 400x400
- TIDY AESTHETIC: The low profile tv wall mounting bracket w/ integrated cable management & optional black snap-on covers keeps flat screen cables organized; ideal for customer-facing digital signage

---

### Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	1.9 in [49 mm]
VESA Hole Pattern(s)	400x400 mm
	400x300 mm

400x200 mm

300x300 mm

300x200 mm

100x100 mm

200x100 mm

200x200 mm

100x150 mm

---

#### Performance

Weight Capacity (Per Display)	77.2 lb [35 kg]
Minimum Display Size	32"
Maximum Display Size	55"
Fits Curved Display	Yes
Video Wall	No
Maximum Arm Extension	19.8 in [503 mm]
Display Tilt	+2 / -12
Swivel / Pivot	+90 / -90
Anti-theft	No

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	24.2 in [61.4 cm]
Product Width	15.7 in [40.0 cm]
Product Height	15.7 in [40.0 cm]
Weight of Product	6.2 lb [2.8 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	12.8 in [32.6 cm]
Package Width	15.5 in [39.4 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	6.9 lb [3.1 kg]

---

#### What's in the Box

Included in Package	1 - wall mount
	4 - VESA extension brackets
	4 - bracket screws
	4 - nuts
	1 - wrench
	4 - M5x14 mm screws
	4 - M6x14 mm screws
	4 - M6x30 mm screws
	4 - M8x30 mm screws
	4 - M8x50 mm screws
	4 - small washers
	4 - large washers
	8 - small spacers
	8 - large spacers
	4 - screws
	4 - concrete screws
	4 - bracket washers
	1 - instruction manual

---

#### Warranty Information

Warranty

5 Years

---

*\*Product appearance and specifications are subject to change without notice.*

