

Compact Mini DisplayPort to DisplayPort Adapter - 4K x 2K Video - UHD Mini DP to DP Converter - mDP to DP 1.2 Adapter - mDP PC/Computer to DisplayPort Monitor/Display - M/F

Product ID: GCMDP2DPMF



The GCMDP2DPMF Mini DisplayPort to DisplayPort adapter/converter allows you to add a standard DisplayPort connection port to your existing laptop or Mac Mini. Easy to use and install, this cost-effective solution makes it easy for you to go from Mini DP to DP, in order to get the most from your Mini DisplayPort device.

Certifications, Reports and Compatibility



Applications

- Allows for an easy connection to a DisplayPort display, using standard DisplayPort cabling
- A Simple and easy way to convert the Mini DisplayPort connector on your laptop into a full size DisplayPort connector

Features

- **MINI DISPLAYPORT to DISPLAYPORT 1.2 ADAPTER:** mDP v1.2 to Standard DP female adapter supports 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **DURABLE AND COMPACT DESIGN:** 4K/Full HD high performance fully molded Mini DisplayPort to DisplayPort adapter with long lasting PVC mold for high strength and reliability; Small 1.4"(37mm)L x 0.9"(22mm)W x

0.4"(11mm)H size for convenience

- **MINI DP TO DP CONVERTER:** This mDP to DP adapter allows you to convert mini-DP port on your laptop/desktop into a standard DP port output; Cost effective way to make the most out of your Mini DisplayPort device
- **APPLICATIONS:** Ideal for home/office/boardroom/classroom works w/laptop (with Mini-DP port)/professional workstations with AMD FirePro W9100/8100, NVIDIA NVS 810/510 graphic card; UHD/4K monitor/projector/display; Microsoft Surface Pro 1-6
- **SPECS:** 1.4"(37mm) L x 0.9"(22mm) W x 0.4"(11mm) H Black DisplayPort v1.2 Mini-DP Male to Standard DP Female port video adapter PVC mold Protocols: HBR 2, MST, GTC Backwards compatible with DP1.1 Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	20
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Physical Characteristics

Color	Black
Product Length	0.9 in [2.2 cm]
Product Width	0.4 in [1.1 cm]
Product Height	1.7 in [4.4 cm]
Weight of Product	0.6 oz [17.0 g]

Packaging Information

Package Quantity	1
Package Length	2.3 in [5.9 cm]
Package Width	3.5 in [8.9 cm]
Package Height	0.7 in [1.8 cm]

Shipping (Package) 0.4 oz [12.0 g]
Weight

What's in the Box

Included in Package 1 - Mini DisplayPort to Display Port Adapter Converter

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

