

## 2.5" to 3.5" Hard Drive Adapter - For SATA and SAS SSDs/HDDs

**Product ID:** 25SATAS35HD



This 2.5" to 3.5" hard drive adapter lets you install a 2.5" SATA or SAS hard drive (HDD) or solid-state drive (SSD) into an internal or external 3.5" drive bay, using standard drive-mounting holes.

The 2.5" to 3.5" hard drive bay adapter lets you install a newer, higher performance drive such as an SSD into a legacy system that may only support a 3.5" hard drive. It provides a cost-efficient way to enhance storage performance and reliability without expensive upgrades to core IT systems. It's also ideal for system administrators who want to build a system that takes advantage of the increased performance of a 2.5" HDD/SSD.

To utilize the full speed potential of your SATA/SAS drive, the adapter supports transfer speeds up to 6Gbps.

You can install the adapter into a desktop, server, storage-array, hot-swap bay, and drive drawer. It offers permanent installation in a 3.5" drive bay with standard mounting holes. When the adapter is installed, you simply slide a 2.5" HDD/SSD into the adapter enclosure, with no tools required.

The adapter is suitable for drives with a height of up to 15 mm. Virtually any 2.5" SATA/SAS drive can be made to look and function like a 3.5" drive.

The adapter includes a label you can use to track and record information about the installed drive.

The 25SATAS35HD is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Install a 2.5" SATA/SAS drive in a 3.5" drive bay

## Features

- Supports 2.5" form factor drives up to 15 mm in height
- Installs into an internal or external 3.5" drive bay; uses standard mounting holes for internal installs
- Tool-less 2.5" drive installation
- Supports SATA I, II and III (up to 6Gbps) and SAS I and II (up to 6Gbps)

---

### Hardware

Warranty	2 Years
Front Door Key Lock	No
Fan(s)	No
Interface	SATA
	SAS
Number of Drives	1
Drive Size	2.5in & 3.5in
Compatible Drive Types	SAS & SATA
Drive Installation	Removable
Number of 2.5 inch bays	1
Supported Drive Height(s)	7mm
	9.5mm
	12.5mm
	15mm

---

### Performance

TRIM Support	Yes
4Kn Support	Yes
S.M.A.R.T. Support	Yes

Type and Rate      SATA/SAS 6 Gbps

Hardware Raid Supported      No

Hot Swap Capability      Yes

#### Connector(s)

Drive Connectors      1 - SFF-8482 (29 pin, Data & Power, Internal SAS)

Host Connectors      1 - SATA Data & Power Combo (7+15 pin)

#### Special Notes / Requirements

Note      Although mobile racks can enable a Serial Attached SCSI (SAS) drive to connect using a standard Serial ATA (SATA) connector, the drive controller must be SAS compatible to properly support SAS drives. SAS controllers can work with SAS and SATA drives, but most SAS drives will only work with a SAS controller.

#### Power

Input Voltage      5V DC / 12V DC

Output Voltage      5 DC

#### Environmental

Operating Temperature      0C to 55C (32F to 131F)

Storage Temperature      -20C to 55C (-4F to 131F)

Humidity      5% ~ 65%

#### Physical Characteristics

Color      Silver & Black

Material      Aluminum and Plastic

Product Length      5.7 in [14.6 cm]

Product Width      4.0 in [10.1 cm]

Product Height      1.0 in [2.6 cm]

Weight of Product      7.9 oz [224.0 g]

#### Packaging Information

Package Quantity	1
Package Length	4.5 in [11.4 cm]
Package Width	6.4 in [16.2 cm]
Package Height	1.5 in [3.9 cm]
Shipping (Package) Weight	9.7 oz [276.0 g]

---

#### What's in the Box

Included in Package	1 - Hard Drive Adapter
	1 - Set of Mounting Hardware
	1 - Quick-Start Guide

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

