

## 3.5in Drive Bay IDE to Single CF SSD Adapter Card Reader - TAA

**Product ID:** 35BAYCF2IDE



This Compact Flash IDE adapter is a perfect solution for accessing CompactFlash (CF I, CF II) and IBM Micro Drive media, allowing you to access the flash/micro drive media as if it were an IDE hard drive.

The CF/IDE adapter can be installed in the computer case through simple mounting in an available 3.5in drive bay, for connection to the computer IDE bus through either a 40 or 44-pin connection.

Designed and constructed to provide a reliable media card platform, the CF IDE adapter is backed by StarTech.com's 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Use your compact flash card as a bootable and removable device
- Excellent for swapping operating systems quickly without having to take your computer apart.
- Connect your compact flash card to a 40 or 44 pin IDE slot

## Features

- Quick and driver free installation into any IDE 40 pin and 44 pin slot
- Fully compatible with Compact Flash Type I/II and IBM Micro-drive
- Allows Compact flash card to be used as bootable storage
- Can be mounted in the front or rear panel of your case, to fit into any 3.5" bay or available expansion slot
- Easy to use jumpers offer simple master/slave drive setting
- Easily swap cards in and out with built-in push button ejector

### Hardware

Warranty	2 Years
----------	---------

Interface	IDE
-----------	-----

### Performance

Maximum Data Transfer Rate	133 MBps
----------------------------	----------

Memory Media Type	CF (Compact Flash I/II Card)
-------------------	------------------------------

### Connector(s)

Drive Connectors	1 - CompactFlash (50 pin) Slot
------------------	--------------------------------

Host Connectors	1 - IDE (40 Pin, EIDE/PATA)
-----------------	-----------------------------

	1 - SP4 (4 pin, Small Drive Power)
--	------------------------------------

### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

### Special Notes / Requirements

Note	This product does not support hot-swapping of flash cards while the PC is powered on. You must turn-off your computer to switch cards.
------	--

### Environmental

Operating Temperature	-55C to 85C (-67F to 185F)
-----------------------	----------------------------

Storage Temperature	-55C to 85C (-67F to 185F)
---------------------	----------------------------

Humidity	5% ~ 85% RH
----------	-------------

---

**Physical Characteristics**

Color	Black
Product Length	3.8 in [97 mm]
Product Width	3.9 in [10 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	4.6 oz [129 g]

---

**Packaging Information**

Package Quantity	1
Package Length	6.8 in [17.3 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.3 in [3.4 cm]
Shipping (Package) Weight	8.5 oz [240.0 g]

---

**What's in the Box**

Included in Package	1 - Compact Flash to IDE Adapter
	1 - 3.5" Enclosure
	1 - Full Profile Expansion Slot Bracket
	1 - SP4 to LP4 Molex Power Cable
	1 - Instruction Manual

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*