

3ft (1m) DB9 to 3.5mm Serial Cable for Serial Device Configuration, RS232 DB9 Male to 3.5mm Cable Used for Calibrating Projectors, Digital Signage, TVs via Audio Jack

**Product ID:** 9M351M-RS232-CABLE



This serial cable features male DB-9 and 3.5mm connectors. It enables remote serial RS232 calibration of TVs, projectors, and digital signage devices that feature a 3.5mm audio jack.

#### High Quality Construction

The aluminum-mylar cable shielding and metal shell connectors mitigate EMI. The molded PVC connectors with strain reliefs and PVC cable jacket prevent damage caused by strain and/or abrasion.

Secure the DB-9 connector by tightening the integrated thumbscrews. These connector screw locks prevent accidental disconnection which could lead to data loss/corruption.

DB9 Serial to 3.5mm Pinout

DB9 Pin 3 to 3.5mm Tip

DB9 Pin 2 to 3.5mm Ring

DB9 Pin 5 to 3.5mm Sleeve

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

#### Certifications, Reports and Compatibility



## Applications

## Features

- **DB9 TO 3.5 MM SERIAL CABLE:** 3ft (1m) RS232 serial control cable enables configuration or calibration of a 3.5mm RS-232 serial devices - Use with TVs, projectors, digital signage displays requiring 3-conductor RS-232 serial control through 3.5mm audio jack
- **QUALITY CONSTRUCTION:** High quality 28 AWG copper wires with Al-Mylar cable shielding and shielded metal shell connectors prevent EMI interference - Molded PVC connectors with strain reliefs and PVC jacket prevent damage due to bends or rough usage
- **COMPATIBILITY:** The DB9 to 3.5mm cable works with USB-A and USB-C to DB9 serial adapters (1P3FP-USB-SERIAL / ICUSB232C) for computers that do not have a built-in serial port Note: DB9 gender changer may be required such as our GC9SF (not included)
- **SPECIFICATIONS:** Length: 3.3ft (1m) - DB9 Male to 3.5 mm Male Serial Cable - Color: Black - 28 AWG - OD: 3.5mm - Jacket: PVC - DB9 Pin 3 to 3.5mm Tip - DB9 Pin 2 to 3.5mm Ring - DB9 Pin 5 to 3.5mm Sleeve
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this product is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC

---

### Performance

Supported Protocols	RS232 Serial
---------------------	--------------

---

### Connector(s)

Connector A	1 - DB-9 (9 pin, D-Sub)
Connector B	1 - 3.5mm Stereo Male 4 pos

---

### Environmental

Operating Temperature	-20 to 60C (-4 to 140F)
Storage Temperature	-20 to 60C (-4 to 140F)
Humidity	30 ~ 75%

---

### Physical

**Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.4 ft [1.0 m]
Product Width	1.3 in [3.3 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	1.4 oz [41.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	5.0 in [12.8 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	0.8 oz [23.0 g]

---

**What's in the Box**

Included in Package	1 - DB9 to 3.5mm RS232 Serial Cable
---------------------	-------------------------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*