

Desk Mount Monitor Arm for up to 34" (17.6lb/8kg) VESA Compatible Displays - Articulating Pole Mount Single Monitor Arm - Ergonomic Height Adjustable Monitor Mount - Desk Clamp/Grommet

**Product ID:** ARMPIVOTB



Save desk space and position your monitor for comfortable viewing with this desk-mount monitor arm, made of heavy-duty steel. It features an articulating arm that enables you to tilt, swivel and rotate your screen, to create a more ergonomic workspace and enhance productivity.

The single monitor mount lets you free up space by suspending your display off of your desk. The VESA mount (75x75, 100x100) monitor arm supports a flat-panel display 13" to 34" in size and up to 17.7 lb. (8 kg) in weight.

With its robust steel construction, the heavy duty monitor arm provides long-lasting performance.

The articulating monitor arm gives you maximum workspace flexibility. You can extend the arm up to 17" (428 mm), swivel 180 degrees and tilt up to 90 degrees to find the perfect viewing angle. The arm offers smooth 360-degree screen rotation, so it's easy to switch from landscape to portrait position. You can also adjust the height of your monitor along the pole to your desired viewing position, to a maximum height of 17.7" (450 mm).

The desk clamp monitor mount makes it easy to mount your VESA mount display above your desk, using the included C-clamp or grommet mount. For easier mounting, the VESA mount features notches that let you pre-set the mounting screw, then slide the monitor in place and tighten the screw. To help keep your work area free of clutter, the monitor arm also features cable management clips that keep your cables neatly out of sight.

The ARMPIVOTB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Create an ergonomic workspace in office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

## Features

- **LARGE MONITOR ARM:** VESA 75x75mm/100x100mm compatible heavy-duty steel single monitor arm supports a 27" (16:9) or 34" (21:9/ultrawide) display up to 17.7lb/8kg; Horizontal articulation & height adjustment
- **RANGE OF ARTICULATION:** Pole mount monitor arm can be positioned/secured along the 17.7" pole and can extend outwards up to 16.85" away from the base; Arm has 2 joints that allow it to swivel +/-180
- **WIDE RANGE OF MOTION:** Ergonomic articulating monitor mount increases comfort & productivity allowing the screen to tilt +/-45, swivel +/-90, rotate 360 (landscape/portrait)
- **SMALL FOOTPRINT:** Desk mount monitor arm with space-saving design enhances the computer work area; built-in cable management clips along the arm & pole keep cables organized for a presentable workspace
- **ADJUSTABLE SET UP:** Use the desk-clamp (C-clamp) or grommet mount to easily mount and tighten by hand to a desktop; Cable management clips can hold incl. tools for quick height & angle adjustment

---

### Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

---

### Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
-------------------------------	----------------

Minimum Display Size	13"
Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Maximum Height	17.7 in [450 mm]
Maximum Arm Extension	16.9 in [428 mm]
Display Tilt	+ 45 / - 45
Swivel / Pivot	180
Display Rotation	360

---

**Special Notes / Requirements**

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 17.7 lb. (8 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 30" (76.2 cm).
------	--

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	18.2 in [462.0 mm]
Product Width	6.3 in [16.0 cm]
Product Height	4.3 in [10.8 cm]
Weight of Product	6.5 lb [3.0 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	19.1 in [48.5 cm]

Package Height 4.6 in [11.7 cm]

Shipping (Package) Weight 8.2 lb [3.7 kg]

---

#### What's in the Box

Included in Package	1 - monitor arm
	1 - pole
	1 - desk clamp
	1 - cable-management clip
	1 - grommet baseplate
	5 - rubber pads
	1 - desk-clamp screw
	1 - grommet plate
	1 - 5 mm hex key
	1 - 6 mm hex key
	4 - M4x12 mm screws
	4 - M5x12 mm screws
	4 - washers
	1 - instruction manual

---

#### Warranty Information

Warranty	5 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*