

25ft (7.5m) Flat High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMIIMM25FL



This Flat High Speed HDMI Cable with Ethernet supports the advanced capabilities of the High Definition Multimedia Interface, including Ethernet data interconnectivity with compatible HDMI devices. The cable features a flat-shaft design that makes it the ideal solution for in-wall installations or installation under carpet or along baseboard.

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Constructed with 28 AWG copper wire, gold-plated connectors, and shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Connect HDMI-equipped devices like LCD TVs, LCD Projectors, Plasma TVs, HDTVs and DVD Players
- Connect multiple devices with one Internet connection (satellite receivers, DVD players, A/V receivers, High

Definition TVs, game consoles and more)

- This quick-connect, single HDMI cable can replace multiple audio and video cables, reducing clutter and hassle, while the flat wire design allows convenient installation under carpets or behind walls

Features

- 3D and Ethernet ready for supported devices
- Supports IP-based applications
- Supports Ultra HD Resolutions up to 4k x 2k
- Supports High Speed HDMI
- Gold-plated HDMI connectors

Hardware

	Warranty	Lifetime
Number of Conductors	19	
Cable Jacket Material	PVC - Polyvinyl Chloride	
Cable Shield Material	Aluminum-Mylar Foil with Braid	

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Special Notes / Requirements

Note	Cable OD: 18mm x 5mm
------	----------------------

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG

Cable Length	25.0 ft [7.6 m]
Product Length	25.0 ft [7.6 m]
Product Width	0.9 in [2.3 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	1.9 lb [0.9 kg]

Packaging Information

Package Quantity	1
Package Length	7.6 in [19.2 cm]
Package Width	7.3 in [18.5 cm]
Package Height	2.0 in [5.1 cm]
Shipping (Package) Weight	2.0 lb [0.9 kg]

What's in the Box

Included in Package	1 - 25 ft Flat High Speed HDMI Cable with Ethernet - HDMI - M/M
---------------------	-----------------------------------------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

***Product appearance and specifications are subject to change without notice.**

