

Desk Mount Triple Monitor Arm - Ergonomic VESA 3 Monitor Mount up to 27" (17.6lb/8kg) - Articulating & Height Adjustable Pole Mount - Tilt/Swivel/Rotate LCD/LED Screen - Desk Clamp/Grommet

Product ID: ARMTRIO



Create the ultimate ergonomic workstation and free up desk space with this desk-mount triple-monitor arm. You can set up three computer monitors (each up to 27") and create a surround setup to maximize productivity.

Enhance your productivity and work in comfort with a multi-screen setup. The triple-monitor mount supports three displays, each 13" to 27" in size. Adjust the position of your monitors with 360 rotation and +30° / -30° tilt for each monitor.

Choose from landscape or portrait screen rotation to customize your workspace. You can set up three displays in landscape position to create a curved surround effect or 'cockpit style' for comfortable viewing. This setup is ideal for editing videos or photos or working with multiple documents. For applications such as web design or coding, you may choose an alternate setup, for example with the center monitor in landscape mode and the outside monitors in portrait position.

Adjust the display height without tools. You simply turn the adjustment knob to adjust the monitor height, keeping all three monitors at the same level.

Made of strong and durable steel, the triple VESA mount monitor stand securely supports three separate computer monitors up to 27", with a weight capacity of up to 17.6 lb. or 8 kg per monitor. The three-monitor stand works with VESA mount monitors (75x75, 100x100).

The triple-monitor arm is easy to set up using the included desk clamp or grommet mount, and comes with cable management clips.

ARMTRIO is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Improve workstation ergonomics in commercial, business and home-office environments
- Create a three-monitor setup using the desk mount or grommet mount
- Ideal for customer service, financial analysis, web design, gaming, photo editing and many other applications

Features

- TRIPLE 27 INCH MONITOR MOUNT: VESA 75x75 or 100x100mm compatible heavy duty steel desktop multi monitor mount supports 3 displays up to 27" (17.6lb/8kg) per screen w/ articulation & height adjustment
- WIDE RANGE OF MOTION: Increase ergonomic comfort with +/-30 tilt & swivel, and 360 rotation; Triple LCD/LED articulating monitor mount with individual micro height adjustment for screen alignment
- THREE MONITORS SIDE-BY-SIDE: Left & right displays can be positioned along their 13.4" arms that can articulate at +30 towards user; Synchronized height adjustability along 17.4" pole (tools incl.)
- FLEXIBLE INSTALLATION: Secure three monitor mount to a desk by hand with the desk-clamp (C-clamp) or grommet mount (10-80mm)
- CABLE MANAGEMENT: Desk mount triple monitor arm with pre-installed and adjustable cable management clips are incorporated onto the pole and monitor arms to keep your computer workspace tidy

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	3
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm)

Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm)

Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	13"
Maximum Display Size	27"
Height Adjustment	Yes
Maximum Height	14.3 in [363 mm]
Maximum Arm Extension	55.6 in [1412 mm]
Display Tilt	+ 30 / - 30
Display Rotation	360

Physical Characteristics

Color	Black
Product Length	4.3 in [11 cm]
Product Width	55.6 in [141.2 cm]
Product Height	21.6 in [54.8 cm]
Weight of Product	13.6 lb [6.2 kg]

Packaging Information

Package Quantity	1
Package Length	11.1 in [28.3 cm]
Package Width	25.7 in [65.3 cm]
Package Height	5.0 in [12.7 cm]
Shipping (Package) Weight	16.5 lb [7.5 kg]

What's in the Box

Included in Package	1 - left monitor arm
---------------------	----------------------

1 - right monitor arm
1 - crossbar
2 - arm caps
1 - pole
1 - desk clamp
2 - end caps
2 - VESA monitor mounts
1 - grommet collar
1 - grommet plate
5 - rubber pads
4 - cable-management clips
2 - thumbscrews
1 - 3 mm Allen key
1 - 5 mm Allen key
12 - M4x14 mm screws
12 - M5x14 mm screws
12 - washers
1 - instruction manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*