

30ft (9.1m) High Speed HDMI Cable – Ultra HD 4k x 2k HDMI Cable – HDMI to HDMI M/M

**Product ID:** HDMM30



This High Speed HDMI Cable is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

#### High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and multi-channel audio, you can enjoy a fully immersive viewing and listening experience.

Constructed with 24 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

### Certifications, Reports and Compatibility



### Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

## Features

- 2x HDMI Male Connectors
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Gold                           |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

### Performance

|                             |                 |
|-----------------------------|-----------------|
| Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
|-----------------------------|-----------------|

### Connector(s)

|             |                   |
|-------------|-------------------|
| Connector A | 1 - HDMI (19 pin) |
| Connector B | 1 - HDMI (19 pin) |

### Physical Characteristics

|                 |                 |
|-----------------|-----------------|
| Color           | Black           |
| Connector Style | Straight        |
| Wire Gauge      | 24 AWG          |
| Cable Length    | 30.0 ft [9.1 m] |
| Cable OD        | 0.4 in [10 mm]  |
| Product Length  | 30.0 ft [9.1 m] |
| Product Width   | 0.8 in [2.0 cm] |
| Product Height  | 0.4 in [1.1 cm] |

|                              |                           |                                              |
|------------------------------|---------------------------|----------------------------------------------|
|                              | Weight of Product         | 2.1 lb [1.0 kg]                              |
| <b>Packaging Information</b> |                           |                                              |
|                              | Package Quantity          | 1                                            |
|                              | Package Length            | 12.6 in [32.0 cm]                            |
|                              | Package Width             | 9.8 in [25.0 cm]                             |
|                              | Package Height            | 2.4 in [6.0 cm]                              |
|                              | Shipping (Package) Weight | 2.2 lb [1.0 kg]                              |
| <b>What's in the Box</b>     |                           |                                              |
|                              | Included in Package       | 1 - 30 ft High Speed HDMI Cable - HDMI - M/M |
| <b>Warranty Information</b>  |                           |                                              |
|                              | Warranty                  | Lifetime                                     |

*\*Product appearance and specifications are subject to change without notice.*