

2U Server Rack Shelf - Universal Rack Mount Cantilever Shelf for 19" Network Equipment Rack & Cabinet - Heavy Duty Steel – Weight Capacity 125lb/56kg - 18" Deep Tray, Black

Product ID: CABSHELFHD



The CABSHELFHD 2U 18in Depth Heavy Duty Fixed Rack Mount Shelf lets you add a high-capacity 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options.

This high-capacity server rack shelf is constructed using SPCC commercial grade cold-rolled steel, providing the additional strength required to hold up to 56kg (125lbs) of equipment - a perfect solution for storing larger, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

Certifications, Reports and Compatibility

Applications

- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- **UNIVERSAL 19" FIT:** This 2U server rack shelf is designed to fit any 19" wide server rack or enclosure including major brands like APC, Dell, Lenovo, HPE and can accommodate your data, IT, networking or other equipment up to 18" (46cm) deep
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures long term durability and supports a total weight of 125lbs/56kg making it the perfect rack shelf solution for any environment

- **THOUGHTFUL DESIGN:** Constructed with upward facing front and rear lips for increased structural integrity and to protect equipment from sliding off the shelf, the lip does not interfere with installation or removal of rack equipment below the shelf
- **VERSATILE FUNCTIONALITY:** At 18in deep, this fixed rackmount shelf is designed to work with any 19 inch cabinet or equipment rack; it provides additional storage space for mission critical hardware, and can even store your tools or audio/video accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 2U server rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Mounting Options	Front Mount (Front Only)

Performance

Weight Capacity (Stationary)	124.7 lb [56.6 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.4 in [44.3 cm]
Internal Depth	18.0 in [45.7 cm]
Product Length	19.0 in [48.3 cm]
Product Width	18.0 in [45.7 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	9.4 lb [4.2 kg]

Packaging Information

Package Quantity	1
------------------	---

Package Length	20.8 in [52.8 cm]
Package Width	21.3 in [54.2 cm]
Package Height	5.1 in [13.0 cm]
Shipping (Package) Weight	12.0 lb [5.4 kg]

What's in the Box

Included in Package	1 - 2U Rack Shelf 8 - M6 Screws 8 - M6 Cage Nuts 8 - M6 Plastic Washers 1 - Quick-Start Guide
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***

