

10"(25cm) Cable Ties - 1/8"(4mm) wide, 2-5/8"(68mm) Bundle Diameter, 50lb(22kg) Tensile Strength, Nylon Self Locking Zip Ties w/Curved Tip, 94V-2/UL Listed, 1000 Pack - White - TAA

Product ID: CBMZT10NK



These Extra-Large cable ties enable you to conveniently bundle and secure multiple cables, to route and organize them. 1000 White cable ties are included, ensuring you'll have plenty on hand.

These plastic electrical cable wraps are 10" (25 cm) in length securing cable bundles up to 2.67" (68 mm) in diameter. They're quick and easy to install or remove, with adjustable tension and a basic one-piece design -- perfect for organizing network cables, power cables, or other cables at your home or office workstation.

Made of durable Nylon 66 material, these cable ties are tough and flexible. They've been rigorously tested to support up to 50 lbs (22.7 kg) of weight & are UL94 V-2 fire rated, UL Approved, and CE & Lloyd's Register Certified.

To suit any application, StarTech.com offers a wide selection of these cable ties in different lengths and colors:

100-pack - 4" (10 cm) Black Cable Ties (CBMZT4B)

100-pack - 4" (10 cm) White Cable Ties (CBMZT4N)

1000-pack - 4" (10 cm) Black Cable Ties (CBMZT4BK)

1000-pack - 4" (10 cm) White Cable Ties (CBMZT4NK)

100-pack - 6" (15 cm) Black Cable Ties (CBMZT6B)

100-pack - 6" (15 cm) White Cable Ties (CBMZT6N)

1000-pack - 6" (15 cm) Black Cable Ties (CBMZT6BK)

1000-pack - 6" (15 cm) White Cable Ties (CBMZT6NK)

100-pack - 8" (20 cm) Black Cable Ties (CBMZT8B)

100-pack - 8" (20 cm) White Cable Ties (CBMZT8N)

1000-pack - 8" (20 cm) Black Cable Ties (CBMZT8BK)

1000-pack - 8" (20 cm) White Cable Ties (CBMZT8NK)

100-pack - 10" (25 cm) Black Cable Ties (CBMZT10B)

100-pack - 10" (25 cm) White Cable Ties (CBMZT10N)

1000-pack - 10" (25 cm) Black Cable Ties (CBMZT10BK)

1000-pack - 10" (25 cm) White Cable Ties (CBMZT10NK)

These cable wraps are backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

Features

- **1000-PACK OF CABLE TIES:** Keep cables organized with 10" (25 cm) White zip ties for 2.67" (68 mm) bundle diameter with Curved Tip; Tool-less installation; UL File Number: E97527
- **INDUSTRIAL STRENGTH:** Made of durable Nylon 66 material, these tough, flexible, adjustable cable ties are tested to support up to 50 lbs (22.7 kg) of weight & are UL94 V-2 fire rated
- **MULTI-LENGTH:** Available in 4" (10 cm) for 0.86" (22 mm) bundle diameter 6" (15 cm) for 1.53" (39 mm) bundle diameter 8" (20 cm) for 2.16" (55 mm) bundle diameter Black or White
- **RELIABLE SAFETY:** 94V-2 Flammability Rating UL Approved CE Lloyd's Register Certified RoHS TAA Compliant
- **REDUCE CLUTTER:** Easy to install, tighten and see, these extra-large plastic electrical cable wraps are ideal for reorganizing your workstation at home or office; StarTech.com 2-year warranty

Physical Characteristics

Warranty	2 Years
Color	White

Material	Nylon 66
Product Length	9.8 in [25.0 cm]
Product Width	0.2 in [0.5 cm]
Product Height	0.1 in [0.2 cm]
Weight of Product	0.1 oz [1.8 g]

Packaging Information

Package Quantity	1000
Package Length	9.4 in [23.9 cm]
Package Width	12.1 in [30.8 cm]
Package Height	3.9 in [10.0 cm]
Shipping (Package) Weight	3.9 lb [1.7 kg]

What's in the Box

Included in Package	1000 - Cable Ties
---------------------	-------------------

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***