

4"(10cm) Cable Ties - 1/16"(2mm) wide, 7/8"(22mm) Bundle Diameter, 18lb(8kg) Tensile Strength, Nylon Self Locking Zip Ties with Curved Tip - 94V-2/UL Listed, 1000 Pack - White - TAA

**Product ID:** CBMZT4NK



These Small cable ties enable you to conveniently bundle and secure multiple cables, to route and organize them. 1000 White cable ties are included, ensuring you'll have plenty on hand.

These plastic electrical cable wraps are 4" (10 cm) in length securing cable bundles up to 0.86" (22 mm) in diameter. They're quick and easy to install or remove, with adjustable tension and a basic one-piece design -- perfect for organizing network cables, power cables, or other cables at your home or office workstation.

Made of durable Nylon 66 material, these cable ties are tough and flexible. They've been rigorously tested to support up to 18 lbs (8.2 kg) of weight & are UL94 V-2 fire rated, UL Approved, and CE & Lloyd's Register Certified.

To suit any application, StarTech.com offers a wide selection of these cable ties in different lengths and colors:

100-pack - 4" (10 cm) Black Cable Ties (CBMZT4B)

100-pack - 4" (10 cm) White Cable Ties (CBMZT4N)

1000-pack - 4" (10 cm) Black Cable Ties (CBMZT4BK)

1000-pack - 4" (10 cm) White Cable Ties (CBMZT4NK)

100-pack - 6" (15 cm) Black Cable Ties (CBMZT6B)

100-pack - 6" (15 cm) White Cable Ties (CBMZT6N)

1000-pack - 6" (15 cm) Black Cable Ties (CBMZT6BK)

1000-pack - 6" (15 cm) White Cable Ties (CBMZT6NK)

100-pack - 8" (20 cm) Black Cable Ties (CBMZT8B)

100-pack - 8" (20 cm) White Cable Ties (CBMZT8N)

1000-pack - 8" (20 cm) Black Cable Ties (CBMZT8BK)

1000-pack - 8" (20 cm) White Cable Ties (CBMZT8NK)

100-pack - 10" (25 cm) Black Cable Ties (CBMZT10B)

100-pack - 10" (25 cm) White Cable Ties (CBMZT10N)

1000-pack - 10" (25 cm) Black Cable Ties (CBMZT10BK)

1000-pack - 10" (25 cm) White Cable Ties (CBMZT10NK)

These cable wraps are backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

## Certifications, Reports and Compatibility



## Applications

## Features

- 1000 STCK KABELBINDER: Ordnen Sie Kabel mit 10 cm langen Weißen Kabelbindern, fr Bndeldurchmesser bis zum 22 mm, mit gebogener Spitze; werkzeuglose Installation; UL Dateinummer: E97527
- 1000-PACK OF CABLE TIES: Keep cables organized with 4" (10 cm) White zip ties for 0.86" (22 mm) bundle diameter with Curved Tip; Tool-less installation; UL File Number: E97527
- INDUSTRIAL STRENGTH: Made of durable Nylon 66 material, these tough, flexible, adjustable cable ties are tested to support up to 18 lbs (8.2 kg) of weight & are UL94 V-2 fire rated
- MULTI-LENGTH: Available in 6" (15 cm) for 1.53" (39 mm) bundle diameter 8" (20 cm) for 2.16" (55 mm) bundle diameter 10" (25 cm) for 2.67" (68 mm) bundle diameter Black or White
- RELIABLE SAFETY: 94V-2 Flammability Rating UL Approved CE Lloyd's Register Certified RoHS TAA Compliant
- REDUCE CLUTTER: Easy to install, tighten and see, these small plastic electrical cable wraps are ideal for reorganizing your workstation at home or office; StarTech.com 2-year warranty

---

### Physical Characteristics

---

Warranty	2 Years
Color	White
Material	Nylon 66
Product Length	3.9 in [10.0 cm]
Product Width	0.1 in [0.2 cm]
Product Height	0.0 in [0.1 cm]
Weight of Product	0.0 oz [0.2 g]

---

**Packaging Information**

Package Quantity	1000
Package Length	5.7 in [14.5 cm]
Package Width	7.7 in [19.6 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	9.7 oz [274.0 g]

---

**What's in the Box**

Included in Package	1000 - Cable Ties
---------------------	-------------------

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

