

10"(25cm) Reusable Cable Ties - 1/4"(7mm) wide, 2-1/2"(65mm) Bundle Dia. 50lb(22kg) Tensile Strength, Releasable Nylon Ties, Indoor/Outdoor, 94V-2/UL Listed, 100 Pack - White - TAA

Product ID: CBMZTRB10



These Extra Large Resealable Cable Ties enable you to conveniently bundle and secure multiple cables, to route and organize them. 100 White cable ties are included, ensuring you'll have plenty on hand.

Reduce Waste and Keep Cables Organized

These plastic electrical cable wraps are resealable and reuseable, enabling you to remove the cable tie, and attach it to different bundle, add additional cables into your bundle, or reroute your cables at any time using the same cable ties, saving you time and cost, while reducing waste. The cable ties are 10" (25 cm) in length securing cable bundles up to 2.55" (65 mm) in diameter. They're quick and easy to install or remove, with adjustable tension and a basic one-piece design -- perfect for organizing network cables, power cables, or other cables at your home or office workstation.

Industrial Strength

Made of durable Nylon 66 material, these cable ties are tough and flexible. They've been rigorously tested to support up to 50 lbs (22.7 kg) of weight & are UL94 V-2 fire rated, UL Approved, and CE & Lloyd's Register Certified.

Available in Different Lengths and Colors

To suite any application, StarTech.com offers a wide selection of these cable ties in different lengths and colors:

100-pack - 5 in. (125 mm) White Cable Ties (CBMZTRB5)

100-pack - 5 in. (125 mm) Black Cable Ties (CBMZTRB5BK)

100-pack - 6 in. (15 cm) White Cable Ties (CBMZTRB6)

100-pack - 6 in. (15 cm) Black Cable Ties (CBMZTRB6BK)

100-pack - 8 in. (20 cm) White Cable Ties (CBMZTRB8)

100-pack - 8 in. (20 cm) Black Cable Ties (CBMZTRB8BK)

100-pack - 10 in. (25 cm) White Cable Ties (CBMZTRB10)

100-pack - 10 in. (25 cm) Black Cable Ties (CBMZTRB10BK)

These reusable cable wraps are backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

Features

- **100-PACK OF REUSABLE CABLE TIES:** Keep cables organized with 10" (25 cm) white zip ties for 2.55" (65 mm) bundle diameter; Tool-less installation and reuse multiple times using the trigger lock release; UL File Number: E97527
- **INDUSTRIAL STRENGTH:** Made of durable Nylon 66 material, these tough, flexible, adjustable, releasable cable ties are tested to support up to 50 lbs (22 Kg) of weight & are UL94 V-2 fire rated at up to 85C
- **MULTI-LENGTH:** Available in 5" (125 mm) for 1.18" (30 mm) bundle diameter 6" (15 cm) for 1.37" (35 mm) bundle diameter 8" (20 cm) for 1.96" (50 mm) bundle diameter Black or White
- **RELIABLE SAFETY:** -40C/-40F to 85C/185F Temperature Rating 94V-2 Flammability Rating UL Approved DNV-GL Maritime Certified ABS Type Approved RoHS TAA Compliant
- **REDUCE WASTE & CLUTTER:** Easily resealable & adjustable these extra large plastic electrical cable wraps are ideal for reorganizing your workstation at home or office; StarTech.com 2-year warranty

Physical Characteristics

Warranty	2 Years
Color	White
Material	Nylon 66
Product Length	9.8 in [25.0 cm]
Product Width	0.3 in [0.8 cm]

Product Height 0.1 in [0.1 cm]

Weight of Product 0.1 oz [2.6 g]

Packaging Information

Package Quantity 100

Package Length 12.2 in [31.0 cm]

Package Width 5.3 in [13.4 cm]

Package Height 2.4 in [6.2 cm]

Shipping (Package) Weight 9.3 oz [264.0 g]

What's in the Box

Included in Package 100 - Cable Ties

Warranty Information

Warranty 2 Years

****Product appearance and specifications are subject to change without notice.***