


## 3m Fiber Optic Cable - Multimode Duplex 62.5/125 LSZH Fiber Jumper Cord - LC/SC

Product ID: FIBLCSC3



The FIBLCSC3 3-meter (10ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

### Certifications, Reports and Compatibility



### Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication

- Used by long distance networks with mission critical data

## Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

---

### Hardware

Warranty	Lifetime
Fiber Size	62.5/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM1

---

### Performance

Maximum Data Transfer Rate	10Gbps
Cable Rating	1Gbps / 10Gbps
Type	Multi Mode

---

### Connector(s)

Connector A	1 - Fiber Optic LC Duplex
Connector B	1 - Fiber Optic SC Duplex

---

### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~90% RH

---

### Physical Characteristics

Color	Orange
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]

---

Product Width	0.5 in [1.3 cm]
Product Height	0.2 in [0.6 cm]
Weight of Product	1.9 oz [54.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.7 in [14.6 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.1 in [2.9 cm]
Shipping (Package) Weight	2.1 oz [60.0 g]

---

**What's in the Box**

Included in Package	1 - 3m Multimode 62.5/125 Duplex Fiber Patch Cable LC - SC
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

