

1ft (30cm) Computer Power Cord, NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

**Product ID:** PXT1011



This 1ft IBM Power Cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Backed by StarTech.com's lifetime warranty, this high quality IBM power cable is constructed to provide a durable, reliable connection.

## Certifications, Reports and Compatibility



## Applications

## Features

- **AC POWER CORD:** This 1ft (30cm) 18AWG flexible computer power cable with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1
- **SPECS:** 1ft (30cm) Power Cable NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT. Jacket Material: PVC. Color: Black. Temperature Range: 37F to 140F (3 to 60). Cable Outer Diameter: 0.25in (6.3mm)

- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

---

**Hardware**

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SVT

---

**Connector(s)**

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

---

**Special Notes / Requirements**

Note	UL Listed
------	-----------

---

**Power**

Input Voltage	125 AC
Input Current	10A

---

**Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	0.9 in [2.3 cm]
Product Height	2.3 in [5.9 cm]
Weight of Product	2.0 oz [58.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.6 in [14.1 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.1 in [2.8 cm]
Shipping (Package) Weight	2.3 oz [66.0 g]

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

