

Monitor Desk Mount for up to 49in 32:9 Ultrawide Curved Screens, Mechanical Spring Arm, C-Clamp/Grommet, Tool-Less Adjustment, Max 44lb/20kg

Product ID: H1M1AG1-MONITOR-ARM



This monitor desk mount creates an ergonomic workspace for productivity and supports up to 49-inch curved monitors, including 21:9 and 32:9 ultrawide displays. The mechanical spring-assisted arm enables multiple adjustment to suit different ergonomic needs.

The spring arm enables a height adjustment range of up to 10.8in (27.6cm) to a maximum height of 20in (50.8cm) with effortless one-touch motion. The monitor arm can extend up to 24.4in (62.1cm) from the base of the desktop mount.

The articulating arm enables 180° pan, and the VESA plate features tool-less adjustments of +/-90° horizontal swivel, -20°/+50° tilt, and 360° screen rotation for portrait or landscape orientations. This flexibility enables users to customize the screen placement for maximum productivity and comfort.

With its steel and aluminum construction, the premium dial monitor arm supports monitors between 4.4 to 44lb (2 to 20kg). This ensures long-lasting stability and reliability, making it ideal for office and home setups.

To maintain an organized workspace, the arms feature a cable management channel along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup.

Certifications, Reports and Compatibility

Applications

Features

- **DESK MOUNT MONITOR ARM:** Single monitor VESA mount (75x75/100x100mm) supports monitors up to 49 inches and 44lb (20kg); Compatible with 16:9 displays as well as 21:9 and 32:9 ultrawide monitors; One-touch tool-less height adjustments up to 10.8in (27.6)
- **DESIGNED FOR CURVED PANELS:** Supports up to 49" curved screen w/max arm height 20in (50.8cm) & max arm reach of 24.4in (62.1cm); VESA plate w/quick release, +/-90 horizontal swivel, -20/+50 tilt, & portrait/landscape support; Articulating arm w/180 pan
- **MOUNTING OPTIONS:** Interchangeable desk C-clamp or grommet mount for desks up to 3.1-inches (8cm) thick for C-clamp and 1.4in (3.5cm) thick for grommet; The monitor stand includes tools to adjust the arm tension to match the monitor weight
- **SAFETY:** The single monitor mount features a rotation stop that prevents the arm from rotating more than +/-90 (180 total), protecting the monitor and surrounding area from accidental impact and ensuring safe operation
- **ORGANIZED WORKSPACE:** Maximize desk space with this computer monitor mount, featuring a mechanical spring arm for smooth and easy adjustments, along with cable management channels along the arms to keep cables out of sight for a tidy setup

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.4 - 3.15in (10 - 80mm) Grommet Diameter: 0.4in - 1.4in (10 - 35mm)

Performance

Weight Capacity (Per Display)	44.1 lb [20 kg]
Minimum Display Size	17"
Maximum Display Size	49" (32:9)

Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Minimum Height	9.1 in [232 mm]
Maximum Height	20.0 in [508 mm]
Minimum Arm Extension	11.5 in [293 mm]
Maximum Arm Extension	24.4 in [621 mm]
Display Tilt	+50 / -20
Display Swivel	+/- 90
Swivel / Pivot	+180 / -180
Display Rotation	360
Anti-theft	No

Special Notes / Requirements

Note	Note: Monitors with a width of less than 40" (50.8 cm) may be used in portrait orientation. However, please be aware that limited desk clearance might restrict monitor rotation.
------	---

Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	5.3 in [13.4 cm]
Product Width	26.1 in [66.3 cm]
Product Height	24.6 in [62.5 cm]
Weight of Product	10.8 lb [4.9 kg]

Packaging Information

Package Length	7.3 in [18.6 cm]
Package Width	17.3 in [44.0 cm]

Package Height	5.1 in [13.0 cm]
Shipping (Package) Weight	12.1 lb [5.5 kg]

What's in the Box

Included in Package	1 - Spring Arm
	1 - Swivel Arm
	1 - Base
	1 - VESA Mount Assembly
	1 - Desk Clamp Bracket, Upper
	1 - Desk Clamp Bracket, Lower
	1 - Grommet Plate
	2 - Clamping Discs
	2 - Clamping Screws
	1 - VESA Mount Nut
	2 - Small Washers
	2 - M4x10mm Screws
	4 - M6x12mm Screw
	1 - M8x35mm Screw
	1 - 4mm Hex Key with Screwdriver
	1 - 6mm Hex Key
	4 - M4x12mm Screws
	4 - M5x12mm Screws
	4 - Large Washers
	1 - User Manual

Warranty Information

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*