

3-Port USB Hub with Ethernet, USB-A Ports, Gigabit Ethernet/GbE, USB 5Gbps, Rugged Design, Bus-Powered, Portable Laptop USB 3.0 Hub

**Product ID:** ST3300G3UA



This USB Hub adds three USB-A 3.2 Gen 1 (5Gbps) ports and one Gigabit Ethernet port to a USB-A enabled desktop or laptop computer. The USB Hub connects to a USB-A port on a computer, using the built-in 10.5in (27cm) host cable. The USB hub is backward compatible with USB 2.0 (480Mbps) devices, ensuring support for a wide range of modern and legacy USB peripherals (e.g., thumb drives, external HDDs/SSDs, HD cameras, mice, keyboards, webcams, and audio headsets). The USB hub is compact in size, facilitating portability when travelling.

The USB hub features a Gigabit Ethernet adapter. The Ethernet controller is compatible with the IEEE 802.3u/ab standards and supports Wake-on-LAN (WoL), Jumbo Frames, and V-LAN Tagging. The network adapter enhances laptop network reliability, security, and performance, by utilizing wired 10/100/1000Mbps Ethernet.

The hub features a rugged yet lightweight housing, so there's no need to sacrifice dependability for portability. With its compact, USB-powered design and a built-in USB cable, you can tuck the combination hub neatly into your travel bag, and avoid the nuisance of carrying multiple separate adapters.

This USB 3.2 Gen 1 hub is perfect for travel, such as back-and-forth trips from home to office. Plus, the compact hub takes up minimal space on a desk, so you can use it in hot-desk or BYOD (Bring Your Own Device) environments.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that is compatible with a wide variety of IT connectivity accessories. The software suite includes:

MAC Address Pass-Through Utility: Improve network security.

USB Event Monitoring Utility: Track and log connected USB devices.

Wi-Fi Auto Switch Utility: Enable users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:  
[www.StarTech.com/connectivity-tools](http://www.StarTech.com/connectivity-tools)

## Certifications, Reports and Compatibility



## Applications

- Connect to a wired, Gigabit network where Wi-Fi is limited or unavailable, such as in boardrooms, classrooms, or hotels
- Add extra USB 3.2 Gen 1 ports and connect your peripherals at home, in the office, or while traveling
- Look trendy and contemporary, and upgrade the connection capabilities of your MacBook, Ultrabook, or laptop

## Features

- **3 PORT USB HUB:** Bus-powered USB 3.2 Gen 1 (5Gbps) expansion hub features a USB-A host connector, 3-Port USB-A hub, rugged aluminum housing, Overcurrent Protection (OCP) & Wake on LAN (WoL)
- **GIGABIT ETHERNET:** Built-in GbE adapter brings the reliability and security of wired RJ45 Ethernet to a laptop or desktop; GbE controller is fully compliant with IEEE 802.3u/ab standards and supports WoL, Jumbo Frames, and V-LAN tagging
- **BUS POWERED USB HUB:** USB Type-A hub w/ speeds up to 5Gbps & shared power up to 4.5W, dependent on power provided by your computer; Supports SSD/thumb drives, data storage, keyboards, mice, web cams, headsets
- **CONNECTIVITY TOOLS:** Optimize the performance and security of this USB-A hub, using the included MAC Address Changer, USB Event Monitoring, Wi-Fi Auto Switch utilities (available for download); Hub compatible with Windows/macOS/Linux/ChromeOS
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this expander hub with multiple USB-A ports is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
USB-C Device Port(s)	No

USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	3
Interface	USB 3.2 Gen 1 (5Gbps) USB 3.2 Gen 1 RJ45 (Gigabit Ethernet)
Bus Type	USB 3.2 Gen 1 (5Gbps)
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3x Flow Control, 802.1q VLAN Tagging, 802.1p Layer 2 Priority Encoding USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	Genesys Logic - GL3523 Realtek - RTL8153

---

#### Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1) 2 Gbps (Ethernet; Full-Duplex)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
Flow Control	Full duplex flow control
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.

---

#### Connector(s)

Connector Type(s)	3 - USB Type-A (9 pin, 5 Gbps) 1 - RJ-45 1 - USB Type-A (9 pin, 5 Gbps)
-------------------	---

---

**Software**

OS Compatibility	Windows 7, 8, 8.1, 10, 11, 11 ARM Windows Server 2008 R2, 2012, 2016, 2019, 2022, 2025 macOS 10.7 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1 Chrome OS
------------------	---

---

**Special Notes / Requirements**

System and Cable Requirements	Host computer with a USB 3.0 port
Note	If connected to a USB 2.0 host port, performance may be limited

---

**Indicators**

LED Indicators	1 - Power 1 - Link/Activity (Network)
----------------	--

---

**Power**

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%~90% RH (Non-condensing)

---

**Physical Characteristics**

Color	Silver & White
Form Factor	Compact
Material	Aluminum and Plastic
Cable Length	10.6 in [268 mm]
Product Length	4.3 in [11 cm]
Product Width	1.3 in [3.4 cm]

Product Height	0.7 in [1.8 cm]
Weight of Product	2.6 oz [73 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.6 in [14.3 cm]
Package Width	6.9 in [17.4 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	4.7 oz [132.0 g]

---

**What's in the Box**

Included in Package	1 - 3-port USB 3.0 hub plus Gigabit Ethernet
---------------------	--

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***