

Portable 4 Port SuperSpeed Mini USB 3.0 Hub - 5Gbps - White - TAA

Product ID: ST4300MINU3W



The ST4300MINU3W Portable 4 Port SuperSpeed Mini USB 3.2 Gen 1 Hub (White) lets you expand your USB connectivity by turning a single USB 3.2 Gen 1 port into four external USB 3.2 Gen 1 ports. The integrated cable design makes this mini USB hub the perfect accessory for your Mac / PC notebook or Ultrabook computer.

The 4 Port USB 3.2 Gen 1 hub supports USB 3.2 Gen 1 data bandwidth (5 Gbps - up to 10x more than USB 2.0) and is backward compatible with USB 2.0 and 1.1 devices, ensuring flawless performance from all of your USB peripherals/devices, regardless of their age.

Ideal for home and business users who require portability, the external USB 3.2 Gen 1 hub is USB-powered and features a rugged, compact design with a built-in cable so no additional cables are needed to connect the hub to your system.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mac or PC notebook / Ultrabook users with limited USB 3.2 Gen 1 ports and multiple USB 3.2 Gen 1 devices

- Make hard to access USB ports more accessible, by being able to position the hub anywhere the cable will reach
- Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

Features

- Four USB type-A ports that can be accessed simultaneously
- SuperSpeed USB 3.2 Gen 1 compliant, with data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Compact and portable design with built-in cable
- Plug-and-Play and hot-swap compatible

Hardware

| | |
|-----------------------|-----------------------|
| Warranty | 2 Years |
| USB-C Device Port(s) | No |
| USB-C Host Connection | No |
| Fast-Charge Port(s) | No |
| Ports | 4 |
| Interface | USB 3.2 Gen 1 (5Gbps) |
| Bus Type | USB 3.2 Gen 1 (5Gbps) |
| Chipset ID | Realtek - RTS5411 |

Performance

| | |
|----------------------------|--------------------------|
| Maximum Data Transfer Rate | 5 Gbps (USB 3.2 Gen 1) |
| Type and Rate | USB 3.2 Gen 1 - 5 Gbit/s |

Connector(s)

| | |
|----------------|--------------------------------|
| External Ports | 4 - USB Type-A (9 pin, 5 Gbps) |
| | 1 - USB Type-A (9 pin, 5 Gbps) |

Software

| | |
|------------------|------------------------------------------------------------|
| OS Compatibility | OS Independent; No additional drivers or software required |
|------------------|------------------------------------------------------------|

Special Notes / Requirements

| | |
|-------------------------------|--------------------|
| System and Cable Requirements | Available USB Port |
|-------------------------------|--------------------|

Indicators

| | |
|----------------|-----------|
| LED Indicators | 1 - Power |
|----------------|-----------|

Power

| | |
|----------------|-------------|
| Power Source | USB-Powered |
| Input Voltage | 5V DC |
| Output Voltage | 5 DC |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 60C (-4F to 140F) |
| Humidity | 0~80% RH |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | White |
| Form Factor | Compact |
| Material | Plastic |
| Cable Length | 5.7 in [145 mm] |
| Product Length | 3.1 in [80 mm] |
| Product Width | 1.4 in [3.6 cm] |
| Product Height | 0.6 in [1.4 cm] |
| Weight of Product | 1.3 oz [38 g] |

Packaging Information

| | |
|------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.2 in [13.3 cm] |
| Package Width | 6.5 in [16.4 cm] |

Package Height 1.7 in [42 mm]

Shipping (Package) Weight 3.8 oz [109 g]

What's in the Box

Included in Package 1 - USB 3.0 hub

1 - quick-start guide

Warranty Information

Warranty 2 Years

**Product appearance and specifications are subject to change without notice.*

