

## 7-Port USB 3.0 Hub (5Gbps) - Desktop

**Product ID:** ST7300USB3B



The ST7300USB3B USB 3.2 Gen 1 Hub lets you add seven external USB 3.2 Gen 1 ports to a computer from a single USB 3.2 Gen 1 host connection.

Offering data transfer rates up to 5 Gbps, the USB hub meets SuperSpeed USB 3.2 Gen 1 specifications and is backward compatible with USB 2.0 and 1.x devices.

Designed for easy port access when connecting or disconnecting devices, the hub features one-sided port orientation, with current overload detection and protection across all seven ports. The hub supports Plug-and-Play and Hot-Swap technologies, letting you switch and operate your connected devices without having to power down the host computer.

The USB hub is bus powered for use in environments where a power outlet may be unavailable, but is perfect for high-power USB devices when used with the included optional power adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Expand your system USB 3.2 Gen 1 capabilities with additional ports
- Make USB ports more accessible by positioning the hub anywhere within cable reach
- Extend the range of USB devices by having the hub act as a mid-point repeater
- Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

## Features

- Seven downstream USB 3.2 Gen 1 ports accessible from one side of the hub, with support for up to 5Gbps
- Universal, multi-platform compatibility, with no additional drivers required
- Plug-and-Play and Hot-Swap compatible
- Backward compatible with USB 2.0 and 1.x devices
- Current overload detection and protection on each USB port
- USB bus powered, includes optional external power adapter for high-power USB devices
- Includes USB 3.2 Gen 1 A to B cable

---

### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	7
Bus Type	USB 3.2 Gen 1 (5Gbps)
Chipset ID	VIA/VLI - VL817

---

### Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
MTBF	43977.72 hours

---

### Connector(s)

Connector Type(s) 1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

7 - USB Type-A (9 pin, 5 Gbps)

#### Software

OS Compatibility OS Independent; No additional drivers or software required

#### Special Notes / Requirements

System and Cable Requirements Available USB 3.0 port

Note If connected to a USB 2.0 host port, performance may be limited

#### Indicators

LED Indicators 7 - Hub Port Connection LEDs

#### Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 1.5 A

Output Voltage 12V DC

Output Current 3 A

Center Tip Polarity Positive

Plug Type M

Power Consumption (In Watts) 36

#### Environmental

Operating Temperature -2C to 52C (29F to 125F)

Storage Temperature -20C to 56C (-4F to 132F)

Humidity 5-95% RH

#### Physical Characteristics

Color Black

Form Factor Desktop

---

Material	Plastic
Product Length	6.8 in [17.2 cm]
Product Width	2.8 in [7 cm]
Product Height	0.9 in [2.3 cm]
Weight of Product	5.2 oz [148 g]

---

#### Packaging Information

Package Quantity	1
Package Length	5.9 in [15.0 cm]
Package Width	8.3 in [21.1 cm]
Package Height	2.5 in [6.3 cm]
Shipping (Package) Weight	1.2 lb [0.5 kg]

---

#### What's in the Box

Included in Package	1 - USB 3.0 Hub
	1 - 3.3 ft [1 m] USB 3.0 Cable
	1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
	1 - Instruction Manual

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*