

DC Power Adapter - 5V, 2A

Product ID: SVA5H2NEUA



This replacement power adapter can provide a power source for any electronic device that has an H type barrel jack and requires 5 volts and up to 2 amps of power.

The adapter is a perfect replacement for the lost or damaged power adapter you've used to power your existing electronics.

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This power adapter is a direct replacement for the power adapters included with the following StarTech.com products:

Dual-Bay 2.5in Hard Drive Enclosure (S252BU33R)

3-Port Portable USB 3.0 Hub plus Gigabit Ethernet (ST3300GU3B)

4 Port Compact Black USB 2.0 Hub (ST4202USB)

4 Port Black USB 2.0 Hub (ST4202USBGB)

7 Port Compact Black USB 2.0 Hub (ST7202USB)

7 Port Black USB 2.0 Hub (ST7202USBGB)

15m USB 2.0 Active Cable with 4 Port Hub (USB2EXT4P15M)

10m USB 3.0 Active Extension Cable (USB3AAEXT10M)

3m USB 3.0 Active Extension Cable (USB3AAEXT3M)

5m USB 3.0 Active Extension Cable (USB3AAEXT5M)

4K HDMI 4-Port Video Splitter (ST124HD4K)

Wireless Display Adapter with HDMI (WIFI2HDMCGE)

4-Port HDMI Automatic Video Switch (VS421HD4K)

The SVA12DN4NEUA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Replace a lost or broken power adapter
- Keep an extra power adapter on hand for your mission-critical devices
- Use a single power adapter as you travel between multiple regions

Features

- Supports a range of devices that require 5 volt and 2 amps (or less) of power and an H-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

Power

Warranty	2 Years
Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4 A
Output Voltage	5 DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

Physical Characteristics

Color	Black
Product Length	4.3 ft [1.3 m]
Product Width	1.5 in [3.9 cm]
Product Height	2.5 in [6.5 cm]
Weight of Product	3.5 oz [100.0 g]

Packaging Information

Package Quantity	1
Package Length	4.0 in [10.1 cm]
Package Width	3.7 in [9.3 cm]
Package Height	2.3 in [5.8 cm]
Shipping (Package) Weight	6.4 oz [180.0 g]

What's in the Box

Included in Package	1 - universal power adapter (NA/JP, EU, UK, AU)
---------------------	---

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

