

25-Pack Universal Laptop Lock 6.6ft (2m), Master Keyed Locking Cable, Compatible w/Noble Wedge/Nano/K-Slot, Anti-Theft Cut-Resistant Cable, TAA

**Product ID:** UNIVMK25-LAPTOP-LOCK



The 25-Pack Universal Laptop Lock is a versatile solution compatible with Noble Wedge, K-Slot (T-Bar), or Nano, providing flexibility and convenience.

#### Adaptable Security

A unique on-the-fly lock tip mechanism enables quickly adapting the lock tip to fit different security slot types. Simply rotate the lock selection dial to change the shape of the lock tip to match the security slot, without requiring additional tools or carry separate lock tips. The cut-resistant steel security cable is 6.6ft (2m) long providing reach and durability.

#### Master Keyed Lock

All 25 locks are master keyed and include a pair of unique keys per lock. This enables streamlined security management of multiple locks for IT administrators. The lock can withstand a pull force of 201lb (91.2kg) for K-slot, 217.8lb (98.8kg) for Nano, and 134.4lb (61.2kg) for Noble Wedge, ensuring the computer or other devices remains safe from theft.

#### Note:

- The Master Key is not included but can be requested with proof of purchase.
- The pull force values mentioned may vary if the security slots do not comply with the design standards specified by their respective manufacturers.

#### Widely Compatible

The versatile bulk-pack security lock is not limited to laptops or notebooks only. Expand the utility of this lock to secure other devices such as docking stations, monitors, printers, SFF computers, projectors, oscilloscopes, or other office and lab equipment. The lock is future-proof and is compatible with old and new computers and peripherals from various brands, including HP, Dell, Microsoft, and more. Spacers are included to protect the device from scuffing or denting the lock slot while ensuring a better fit to the device.

## Full-Motion Lock Design

The diameter of the lock head is 0.5in (14mm) and features a ball joint design that allows for 360 rotation and 90 pivot of the lock head. This flexibility reduces coiling and minimizes strain on the notebook slot, enhancing durability and usability.

## Certifications, Reports and Compatibility



## Applications

- Lock selection dial enables quick selection of the lock tip without disassembly or additional adapters
- 25-pack is ideal for IT professionals facilitating multiple setups
- Streamline security management with a Master Key, available by request

## Features

- 3-IN-1 LAPTOP LOCK: This TAA-compliant universal lock is compatible with Noble Wedge, K-Slot (T-Bar), and Nano lock slots using an adjustable lock tip; 6.6ft (2m) thick cut-resistant cable; The 25-pack is ideal for IT administrators managing multiple setups
- MASTER KEY ON DEMAND: Each lock comes w/ a unique key for individual lock access; IT Managers or designated key holders have the option to order a master key (sold separately, with proof of purchase) to unlock any lock without managing multiple keys
- COMPATIBILITY: Bulk-pack universal locking cable for laptop works with HP, Dell, Microsoft, and others; Notebook anti-theft lock is not brand-specific for future-proof compatibility with industry-standard security slots; Secure office and lab equipment
- CLEVER DESIGN: Ball joint enables 360 rotation, and the elbow's joint 90 pivot helps reduce coiling & minimize strain on the slot; Included spacers prevent scuffing & improve fitting; Carbon steel cable can withstand a pull force up to 134.4lb (61.2kg)
- FLEXIBLE INSTALLATION: Included hook & loop strap keeps portable notebook cable lock organized; Accessorize with anchor locks LTANCHOR, KSLTAD, and LTANCHORL (sold separately) to safeguard equipment that lacks a security slot

---

### Hardware

Warranty	2 Years
Compatible Lock Slot	Kensington Standard Slot (K-Slot)

Noble Wedge Slot

Kensington Nano Slot

---

#### Performance

Anti-theft	Yes
------------	-----

---

#### Special Notes / Requirements

Patents and Licenses	The Master Key is not included but can be requested with proof of purchase
	The pull force values mentioned may vary if the security slots do not comply with the design standards specified by their respective manufacturers.

---

#### Environmental

Operating Temperature	-20C to 40C (-4F to 104F )
Storage Temperature	-20C to 65C (-4F to 149F )
Humidity	0 to 95% RH

---

#### Physical Characteristics

Color	Silver & Black
Construction Material	Steel and Plastic
Product Length	6.7 ft [2.0 m]
Product Width	0.6 in [1.4 cm]
Product Height	1.3 in [3.2 cm]
Weight of Product	4.4 oz [125.0 g]

---

#### Packaging Information

Package Quantity	25
Package Length	10.2 in [25.8 cm]
Package Width	13.1 in [33.3 cm]
Package Height	5.0 in [12.7 cm]
Shipping (Package)	8.5 lb [3.9 kg]

Weight

---

**What's in the Box**

Included in Package	25 - Laptop Security Lock
	25 - Pairs of Keys
	75 - Lock Spacers
	25 - Hook-and-Loop Strap
	25 - Quick-Start Guide

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

