

Travel A/V Adapter: 2-in-1 Mini DisplayPort to HDMI or VGA Converter

**Product ID:** MDP2HDVGA



This travel adapter lets you connect your mDP enabled Ultrabook or laptop computer to any VGA or HDMI display. The 2-in-1 Mini DisplayPort adapter is the perfect accessory for any of your Microsoft Surface Pro devices equipped with mDP.

Why carry multiple adapters when you only need one? Instead of keeping two different adapters on-hand, the MDP2HDVGA mDP travel adapter offers both VGA and HDMI outputs, so you'll be able to connect from your laptop mDP output to any modern boardroom or classroom display -- an ideal plug-and-play solution for BYOD (Bring Your Own Device) applications at the office.

Plus, because the converter supports video resolutions up to 1920x1200 or 1080p you can convert a Mini DisplayPort video source to HDMI or VGA without sacrificing video quality.

The travel A/V adapter maximizes portability with a small footprint and lightweight design. The convenient design ensures the adapter is as portable as your laptop, fitting easily into your laptop bag or carrying case and eliminates the need to carry more than one adapter. With this adapter you can walk into virtually any boardroom ready to present, making a great first impression, and saving you the embarrassment of having to rummage through your bag looking for the right connector.

The 2-in-1 converter is compatible with the Intel Thunderbolt port on your computer and installs easily with no software or drivers required.

The MDP2HDVGA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility





## Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD laptop/Ultrabook to a provided HDMI, or VGA display at work
- Connect a VGA, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

## Features

- 2-in-1 design lets you connect your mDP computer to any HDMI or VGA display using a single adapter
- Maximize portability with a compact, lightweight adapter you can easily carry in your laptop bag
- Supports video resolutions up to 1920x1200 or 1080p
- Compatible with Intel Thunderbolt
- Plug-and-play installation
- No power adapter required

---

### Hardware

Warranty	3 Years
AV Input	Mini DisplayPort - 1.2
AV Output	HDMI - 1.4
	VGA
Audio	Yes

---

### Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital Resolutions	1920x1200/1080p

Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio
MTBF	1,097,978 hours

---

**Connector(s)**

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - HDMI (19 pin)
	1 - VGA (15 pin, High Density D-Sub)

---

**Special Notes / Requirements**

Note	<p>The HDMI port is a passive port.</p> <p>The VGA port is an active port.</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	---

---

**Environmental**

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10~85% RH

---

**Physical Characteristics**

Color	Black
Cable Length	5.9 in [150 mm]
Product Length	7.5 in [19.0 cm]
Product Width	2.3 in [5.8 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.8 oz [22.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	4.6 in [11.8 cm]

Package Width 7.8 in [19.9 cm]

Package Height 0.7 in [1.7 cm]

Shipping (Package) Weight 1.5 oz [42.0 g]

---

**What's in the Box**

Included in Package	1 - Mini DisplayPort to HDMI / VGA Adapter
	1 - Instruction manual

---

**Warranty Information**

Warranty	3 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

