

USB-C to Gigabit Ethernet Adapter, White, Thunderbolt 3 Compatible, Windows & Mac, RJ45 LAN Network Converter

Product ID: US1GC30W



Now you can easily connect to a Gigabit network through the USB-C or Thunderbolt 3 port on your laptop or desktop computer. This Gigabit Ethernet (GbE) network adapter provides a reliable network connection without even having to install drivers. It's ready to go, with native driver support to ensure a quick setup.

The USB Type-C network adapter supports full Gigabit bandwidth by harnessing the performance of USB3.2 Gen 1 (5 Gbps). You can access very large files over the network at Gigabit speeds.

Get up and running quickly. Simply plug the adapter into the USB-C port on your laptop and connect to your network. The network adapter chipset provides native driver support, so you don't have to worry about installing additional software.

The USB Type-C connector is smaller and easier to use than previous USB connectors. It's a reversible plug so you can connect to your devices with either side facing up. You can insert the cable the right way every time - without frustration or the risk of port damage.

Compact and portable, this USB Gigabit network adapter is the ideal desktop network adapter or laptop accessory. It's powered directly from the USB port making it easy to connect when you're on the go. Plus, its lightweight design makes the adapter the perfect travel accessory for your Chromebook Pixel or MacBook.

The US1GC30W features a white design that looks great with your Apple Mac and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Add Gigabit Ethernet capabilities to your MacBook or Chromebook Pixel
- Turn your USB-C port into a Gigabit LAN

Features

- **USB-C NETWORK ADAPTER:** USB-C to RJ45 adapter adds an Ethernet port to your computer supporting up to Gigabit speeds on 10/100/1000 Mbps Networks; Ideal for reliable wired gigabit network connections, or as an alternative to WiFi
- **FULL FEATURED:** USB-C to Ethernet dongle; Uses Realtek RTL8153 Chipset for native compatibility with laptop, desktops, and 2-in-1 computers; Compatible with USB C, Thunderbolt 3 and Thunderbolt 4
- **OS COMPATIBILITY:** USB NIC adapter for laptop offers plug and play connectivity (no driver install required); Works with Windows versions 7 and up, Windows Server, macOS 10.14 and up, Linux distributions with kernel 4.11 and up (LTS only), and Chrome OS
- **VERSATILE DESIGN:** With its compact and lightweight design for maximum portability, this USB Type-C NIC/Gigabit network adapter enables you to securely connect your laptop to a Gigabit Ethernet network wherever you go; USB bus-powered
- **TECHNICAL SPECS:** USB 3.2 Gen 1 Type-C (5 Gbps); Compatible with USB 3.0/2.0; 1x RJ45 Port; Attached Cable; 10/100/1000 Mbps; Realtek RTL8153 Chipset ; 9K Jumbo Frames; VLAN Tagging; Wake-on-LAN; Color: White

Hardware

Warranty	2 Years
Ports	1
Interface	RJ45 (Gigabit Ethernet)
Bus Type	USB 3.2 Gen 1 (5Gbps)

Industry Standards IEEE 802.3, 802.3u and 802.3ab

Chipset ID Realtek - RTL8153

Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet - Full-Duplex)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
External Ports	1 - RJ-45

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11, 11 ARM Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022, 2025 macOS 10.7 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1VLAN tagging is currently not supported in macOS Linux Kernel 2.6.25 and up - LTS Versions only Chrome OS
------------------	---

Special Notes / Requirements

Note	Jumbo Frames are no longer supported in macOS
------	---

Power

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0C to 45C (32F to 113F)
-----------------------	-------------------------

Storage Temperature -10C to 70C (14F to 158F)

Humidity 10%-85% RH

Physical Characteristics

Color	White
Form Factor	Attached Cable
Material	Plastic
Cable Length	4.9 in [125 mm]
Product Length	8.5 in [215 mm]
Product Width	1.1 in [27.5 mm]
Product Height	0.6 in [16 mm]
Weight of Product	0.8 oz [24.0 g]

Packaging Information

Package Quantity	1
Package Length	4.8 in [12.2 cm]
Package Width	8.2 in [20.8 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	1.3 oz [36.0 g]

What's in the Box

Included in Package	1 - USB-C to GbE network adapter
---------------------	----------------------------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*